

2m (6 ft) White Mini DisplayPort to DisplayPort 1.2 Adapter Cable M/M - DisplayPort 4k

Product ID: MDP2DPMM2MW



The MDP2DPMM2MW 2m White Mini DisplayPort™ to DisplayPort Adapter Cable, features a Mini DP male connector on one end, and a DP male connector on the other, allowing you to connect any Mini DisplayPort-equipped laptop (including the Mac® family of products) to an HDTV, monitor or projector that uses a standard DisplayPort connection.

The mDP to DP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDP2DPMM2MW is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please Note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DP to DP Cables can be connected to the Thunderbolt ports, enabling you to connect your DP compatible displays.

Certifications, Reports and Compatibility



Applications

- Connect a DisplayPort monitor or projector to devices equipped with a Mini DisplayPort connection port

Features

- High-resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Designed and manufactured to DisplayPort 1.2 standards
- Color: White
- Backward compatible with DisplayPort 1.1
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Gold-plated connectors

| | | |
|---------------------------------|-----------------------------|---|
| Hardware | Warranty | Lifetime |
| | Cable Jacket Type | PVC - Polyvinyl Chloride |
| | Cable Shield Type | Aluminum-Mylar Foil with Drain |
| | Connector Plating | Gold |
| | Fire Rating | CMG Rated (General Purpose) |
| | Number of Conductors | 19 |
| Performance | Maximum Digital Resolutions | 4k x 2k (3840 x 2160) @ 60Hz |
| Connector(s) | Connector A | 1 - Mini-DisplayPort (20 pin) Male |
| | Connector B | 1 - DisplayPort (20 pin) Male |
| Physical Characteristics | Cable Length | 6.6 ft [2 m] |
| | Color | White |
| | Connector Style | Straight |
| | Product Length | 6.6 ft [2 m] |
| | Product Weight | 3 oz [85 g] |
| | Wire Gauge | 32 AWG |
| Packaging Information | Package Quantity | 1 |
| | Shipping (Package) Weight | 0.2 lb [0.1 kg] |
| What's in the Box | Included in Package | 1 - 2 m White Mini DisplayPort to DisplayPort 1.2 Adapter Cable - M/M |

Product appearance and specifications are subject to change without notice.