

## 2m High Speed HDMI Cable with Ethernet - Ultra HD 4k x 2k HDMI Cable - HDMI to HDMI M/M

Product ID: HDMM2MHS



The HDMM2MHS 2-meter High Speed HDMI® Cable with Ethernet supports the advanced capabilities of the High-Definition Multimedia Interface, including Ethernet data inter-connectivity with compatible HDMI-enabled products, and is fully backward compatible with older HDMI-capable devices.

The cable features gold-plated HDMI (male) connectors which help to ensure a high quality digital connection capable of transmitting high-definition video and multi-channel audio between devices such as Blu-Ray Disc™ players, HDTVs, DVD Players, DVRs, stereo receivers and more.

This high quality HDMI cable fully supports 1080p+ resolutions at up to 120Hz refresh rate, with life-like color. To accommodate the demands of future high definition devices, such as increased resolutions and higher frame rates, this Ultra HD cable supports resolutions up to 4k x 2k.

All StarTech.com High Speed HDMI Cables are expertly designed and constructed of top quality materials to deliver dependable high-definition performance, and are backed by Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Quick-connect single HDMI® cable replaces multiple audio and video cables, reducing clutter and hassle
- Connecting high-definition A/V devices such as Blu-Ray Disc™ players, HDTVs, DVRs, etc.
- Connecting HDMI-equipped devices such as DVD players, game consoles, etc.
- Enables multiple devices to share an Internet connection (where applicable, device must support High Speed HDMI® with Ethernet)

### Features

- Gold-plated HDMI® connectors
- High quality construction
- 3D and Ethernet ready (for supported devices)
- Supports Ultra HD Resolutions up to 4k x 2k

<b>Hårdvara</b>	Warranty	Lifetime
	Antal ledare	19
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kontaktplätering	Guld
<b>Prestanda</b>	Maximal digital upplösning	4K x 2K @ 30 Hz
<b>Kontakt(er)</b>	Connector A	1 - HDMI (19-stifts) Hane
	Connector B	1 - HDMI (19-stifts) Hane
<b>Utseende</b>	Färg	Svart
	Kabellängd	2 m [6.6 ft]
	Kontakttyp	Rak
	Produktbredd	0.000
	Produkthöjd	0.000
	Produktlängd	2 m [6.6 ft]
	Produktvikt	110.2 g [3.9 oz]
	Tråddimension	28 AWG
	Yttre kabelldiameter	7.3 mm [0.3 in]
<b>Förpackning</b>	Förpackningsantal	1
	Fraktvikt (förpackning)	119.7 g [4.2 oz]
	Package Height	10 mm [0.4 in]
	Package Length	20 cm [7.9 in]
	Package Width	22 cm [8.7 in]
<b>Vad det är i lådan</b>	Ingår i paketet	1 - 2m High Speed HDMI® Cable with Ethernet - HDMI - M/M

Product appearance and specifications are subject to change without notice.