

Mini DisplayPort to DVI Video Adapter Converter - White

Product ID: MDP2DVIW



The MDP2DVIW passive Mini DisplayPort® to DVI Adapter (White) offers an easy-to-use DVI/Mini-DisplayPort link that enables you to connect a DVI computer monitor to a device with a Mini-DisplayPort output (such as a laptop video out port) or video card. The adapter is the perfect accessory for any of your MacBook® or Microsoft® Surface™ Pro devices with mDP.

The adapter supports high resolution output up to 1920x1200, offering a cost-effective solution for mirroring or extending a computer desktop onto a second display. Plus, because the adapter functions passively, it can be used with a DVI to HDMI adapter, to connect an HDMI-equipped monitor to a Mini DisplayPort output.

This versatile Mini DisplayPort to DVI adapter requires a multimode DisplayPort port (DisplayPort ++) connection to function, and is compatible with Intel® Thunderbolt™ output when directly connected to a supporting DisplayPort over Thunderbolt I/O port.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade shows using DVI displays
- Keep your existing DVI monitor for use with your new Mini DisplayPort® device
- Ideal for using a DVI monitor as a secondary display connected through a Mini DisplayPort output

Features

- Easy to use cable, no software required
- Supports resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Compatible with Intel® Thunderbolt™

Hardware	Warranty	3 Years
	Active or Passive Adapter	Passive
	Adapter Style	Adapters
	Audio	No
	AV Input	DisplayPort
	AV Output	DVI
	Industry Standards	DisplayPort 1.1a DVI 1.1
Performance	Maximum Digital Resolutions	1920x1200 / 1080p
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - DVI-I (29 pin) Female
Environmental	Humidity	40~85% RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	4.7 in [120 mm]
	Color	White
	Enclosure Type	Plastic
	Product Height	0.6 in [1.5 cm]
	Product Length	7.1 in [18 cm]
	Product Width	1.8 in [45 mm]
	Weight of Product	1 oz [29 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	1.5 oz [43 g]
What's in the Box	Included in Package	1 - Mini DisplayPort® to DVI Converter

Product appearance and specifications are subject to change without notice.