

6 ft Mini DisplayPort 1.2 Cable M/M - Mini DisplayPort 4k

Product ID: MDISPLPORT6



The MDISPLPORT6 6ft Mini DisplayPort™ 1.2 cable features 2 Mini DP male connectors, and offers a dependable solution for connecting any Mini DisplayPort-enabled laptop (including Mac® family of products) to a Mini DisplayPort-equipped monitor.

The mDP cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDISPLPORT6 is backed by StarTech.com's Lifetime Warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

Please note: Newer laptop and desktop computers (e.g. Apple®) come equipped with Thunderbolt™ ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

Certifications, Reports and Compatibility



Applications

- Connect your Mini DisplayPort laptop or desktop to a Mini DisplayPort compatible display

Features

- High resolution support of up to 4k x 2k
- Support for High Bit Rate 2 (HBR2) bandwidth of up to 21.6 Gbps
- Designed and manufactured to DisplayPort 1.2 standards
- Backward compatible with DisplayPort 1.1
- Supports the DPCP (DisplayPort Content Protection) standard in addition to HDCP
- Gold-plated connectors

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	19
Performance	Maximum Digital Resolutions	4k x 2k (3840 x 2160) @ 60Hz
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - Mini-DisplayPort (20 pin) Male
Environmental	Humidity	0~75% RH
	Operating Temperature	-20°C to 50°C (-4°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	6 ft [1.8 m]
	Cable OD	0.2 in [4.8 mm]
	Color	Black
	Product Length	6 ft [1.8 m]
	Product Weight	2.2 oz [62 g]
	Wire Gauge	32 AWG
Packaging Information	Shipping (Package) Weight	2.5 oz [71 g]
What's in the Box	Included in Package	1 - 6ft Mini DisplayPort Cable - M/M

Product appearance and specifications are subject to change without notice.