


4 port PCI 1394a FireWire Adapter Card - 3 External 1 Internal

Product ID: PCI1394MP



This 4 Port (3 External/1 Internal) PCI 1394 FireWire Adapter Card lets you connect iPods, MP3 players, portable drives, digital camcorders and more to your desktop computer.

The FireWire adapter card supports hot-swapping, so you'll be able to plug, unplug, and swap your FireWire peripherals with ease.

Guaranteed to work with both PCs and Macs, the 4 port PCI FireWire Adapter Card is backed by StarTech.com's Lifetime Warranty and FREE LIFETIME tech support. Plus, the adapter provides both standard profile and low profile/half-height brackets for adapting to slimline or small form factor system applications.

Please Note: If you require digital video editing software, StarTech.com offers a complete FireWire kit with our [PCI1394_4](#) card. This software is compatible with Windows operating systems only.

WHQL Certified - Designed to work with Microsoft Windows XP

Certifications, Reports and Compatibility



Applications

- Add a high-speed FireWire port to a full or small form factor desktop without any FireWire ports
- Connect a digital camera to a desktop with a PCI slot to download photos and video
- Connect an external FireWire hard drive or optical drive to a PCI-enabled system

Features

- 3 external, 1 shared internal FireWire400 port, with supported data transfer rates up to 400 Mbps
- Compliant with IEEE 1394a - 2000 as well as 1394-1995 standards
- Includes Low Profile installation bracket
- Plug-and-Play and hot-swap compatible

Hardware	Warranty	Lifetime
	Bus Type	PCI (5 Volt)
	Card Type	Standard Profile (LP bracket incl.)
	Chipset ID	Texas Instruments - TSB12LV26
	Industry Standards	IEEE 1394a
		OHCI
		PCI 2.1
Interface	FireWire 400 (1394a)	
Ports	4	
Performance	Maximum Data Transfer Rate	400 Mbps
Connector(s)	Connector Type(s)	1 - PCI (5V, 32-bit) Male
	External Ports	3 - FireWire 400 (6 pin, IEEE 1394a) Female
	Internal Ports	1 - FireWire 400 (6 pin, IEEE 1394a) Female
Software	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2016 Mac OS X® 10.x (tested up to 10.4) Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
Physical Characteristics	Product Height	3.1 in [8 cm]
	Product Length	4.8 in [12.3 cm]
	Product Weight	2.5 oz [70 g]
	Product Width	0.7 in [18 mm]
Packaging Information	Shipping (Package) Weight	0.2 lb [0.1 kg]
What's in the Box	Included in Package	1 - PCI FireWire Card
		1 - Low Profile Bracket
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.