

2 Port PCI Parallel Adapter Card - EPP/ECP

Product ID: PCI2PECP



The PCI2PECP 2 Port EPP/ECP PCI Parallel Adapter Card can be installed in an available PCI slot, adding two IEEE 1284 ports to your PC and supporting data transfer speeds of up to 1.5 Mbps (up to 3 times faster than built-in parallel ports).

Installing the EPP/ECP parallel adapter card is easy, with support for Windows® 8, 7, Vista, XP, ME, 98SE, 95, DOS, Windows Server® 2012, and Linux. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

A complete dual profile solution, this parallel adapter card provides both a standard bracket and a low-profile/half-height bracket for adapting to slimline or small form factor system applications.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Includes half-height/low profile mounting bracket
- Easy plug and play installation
- Data transfer rates of up to 1.5 Mbps
- Compatible with Linux and all versions of Windows® including Windows® XP
- IRQ sharing eliminates conflicts between multiple cards
- Supports EPP, ECP, SPP and BPP
- Installation scripts available for Linux RedHat 7.2, SuSE 7.3 and Mandrake 8.2

Hardware	Warranty	Lifetime
	Bus Type	PCI / PCI-X (5 / 3.3V)
	Card Type	Standard Profile (LP bracket incl.)
	Chipset ID	ASIX - MCS9815CV
	Industry Standards	IEEE-1284
	Interface	Parallel
	Port Style	Integrated on Card
	Ports	2
Performance	Maximum Data Transfer Rate	1.5 Mbps
	Supported Protocols	EPP, ECP, SPP, BPP, PS2
Connector(s)	Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V, 32-bit) Male
	External Ports	2 - DB-25 (25 pin, D-Sub) Female
Software	OS Compatibility	Windows® DOS, 95, 98SE, ME, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
Special Notes / Requirements	System and Cable Requirements	Unused PCI slot
Physical Characteristics	Product Height	4.7 in [120 mm]
	Product Length	4.7 in [120 mm]
	Product Weight	2.5 oz [70 g]
	Product Width	0.8 in [20 mm]
Packaging Information	Shipping (Package) Weight	0.5 lb [0.2 kg]
What's in the Box	Included in Package	1 - 2 Port PCI Parallel Card
		2 - Low Profile Brackets
		1 - Ribbon Cable w/DB25F Plate
		1 - Driver CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.