

Mini DisplayPort to VGA Video Adapter Converter - White

Product ID: MDP2VGAW



This Mini DisplayPort to VGA adapter lets you connect your mDP computer to a VGA monitor or projector. The adapter works with Mini DisplayPort computers like your MacBook or Microsoft® Surface.

Easily connect your Mini DisplayPort computer to a VGA display

The mDP to VGA adapter lets you connect your Mini DisplayPort laptop, desktop or tablet to a VGA display. The adapter is compatible with mDP ports as well as Thunderbolt 1 and Thunderbolt 2 I/O ports, and supports plug-and-play connectivity ensuring a hassle-free setup.

Works with legacy VGA monitors

The Mini DisplayPort adapter makes your mDP computer fully compatible with existing VGA monitors or projectors in your home or around your office. The VGA connector features nuts that mate with the screws on standard VGA cables, to ensure your video cable won't get disconnected.

The perfect travel companion for your MacBook with Mini DisplayPort

With its all-white design, this Mini DisplayPort video adapter is the perfect travel accessory for your MacBook with mDP. The adapter is compact and lightweight so it fits easily into your MacBook bag or carrying case, which is great for BYOD (Bring Your Own Device) applications at the office. While the adapter looks great next your Mac it also works with any Mini DisplayPort computer, such as your Windows® laptop.

Crystal-clear picture quality

With support for video resolutions up to 1920x1200 or 1080p, you'll be surprised at the picture quality the adapter provides, even when connected to a legacy VGA monitor, projector or television. The adapter harnesses the video capabilities built into your mDP connection to deliver every detail in stunning high-definition.

The MDP2VGAW is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for digital entertainment centers, home offices, business conference rooms and trade show displays
- Keep your existing VGA monitor to be used with your new Mini-DisplayPort device
- Ideal for using your VGA monitor as a secondary display

Features

- Supports PC resolutions up to 1920x1200 and HDTV resolutions up to 1080p
- Easy to use adapter, no software required
- Compatible with Intel® Thunderbolt™

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	Audio	No
	AV Input	DisplayPort
	AV Output	VGA
	Industry Standards	DisplayPort 1.1a
Performance	Maximum Analog Resolutions	1920x1200
Connector(s)	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
Environmental	Humidity	40~85% RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
Physical Characteristics	Cable Length	4.7 in [120 mm]
	Color	White
	Enclosure Type	Plastic
	Product Height	0.6 in [15 mm]
	Product Length	7.1 in [180 mm]
	Product Weight	1 oz [28.5 g]
	Product Width	1.8 in [45 mm]
Packaging Information	Shipping (Package) Weight	1.5 oz [42 g]
What's in the Box	Included in Package	1 - Mini DisplayPort® to VGA adapter

Product appearance and specifications are subject to change without notice.