

## Mini DisplayPort Extension Cable M/F - 1,8m (6 ft.) - 4k

Product ID: MDPEXT6



This Mini DisplayPort™ 1.2 cable lets you extend the connection distance between your Mini DP devices by up to 6 feet.

### Position your devices the way you want

The cable delivers the ideal solution for better placement of peripheral devices and can be used to connect your Microsoft Surface™ Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, and other mDP enabled devices to Apple's LED Cinema Display or other Mini DisplayPort monitor.

Simply connect your tablet or laptop to the extension cable using a standard Mini DisplayPort Cable and connect the extension cable to your Mini DP monitor.

## Provide astonishing picture quality

The cable supports high resolutions of up to 4k x 2k (3840 x 2160) @ 60Hz with a maximum HBR2 bandwidth of 21.6 Gbps. The cable also supports Multi-Stream (MST) for daisy chaining multiple monitors and provides optional audio support.

The MDPEXT6 is backed by StarTech.com's lifetime warranty, for guaranteed reliability and ensures that digitally protected content is displayed properly, with both HDCP and DPCP capability.

**Please note:** Newer laptop and desktop computers (e.g. Apple) come equipped with Thunderbolt™ ports only. Our Mini DisplayPort Cables can be connected to the Thunderbolt ports, enabling you to connect your Mini DP compatible displays.

### Certifications, Reports and Compatibility



### Applications

- Extend the connection distance between your Microsoft Surface Pro 4, Surface Book, MacBook, MacBook Pro, MacBook Air, Mac Pro, iMac, or Mac Mini and Apple LED Cinema Display monitor, by 6 feet

### Features

- Provides a clear digital audio video signal
- Guaranteed reliability with our lifetime warranty

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Gold
	Fire Rating	CMG Rated (General Purpose)
	Number of Conductors	20
<b>Connector(s)</b>	Connector A	1 - Mini-DisplayPort (20 pin) Male
	Connector B	1 - Mini-DisplayPort (20 pin) Female
<b>Physical Characteristics</b>	Cable Length	6 ft [1.8 m]
	Color	Black
	Connector Style	Latching
	Product Length	6 ft [1.8 m]
	Weight of Product	2.6 oz [75 g]
	Wire Gauge	32 AWG
<b>Packaging Information</b>	Package Height	0.7 in [18 mm]
	Package Length	8.7 in [22 cm]
	Package Quantity	1
	Package Width	7.9 in [20 cm]
	Shipping (Package) Weight	3 oz [84 g]
<b>What's in the Box</b>	Included in Package	1 - 6 ft Mini DisplayPort 1.2 Video Extension Cable - M/F

Product appearance and specifications are subject to change without notice.