

4 Port PCI 1394a FireWire Adapter Card with Digital Video Editing Kit

Product ID: PCI1394_4



This 4 Port PCI IEEE 1394 FireWire 400 Adapter Card turns a motherboard PCI slot into four IEEE 1394a FireWire 6-pin female ports (1 internal, 3 external) - a cost-effective solution that lets you connect any FireWire 400 device that uses a 6-pin connector to your desktop computer.

The card can be installed in either Mac or PC computers, providing a practical solution for connecting iPods, MP3 players, portable drives, digital camcorders and more. The adapter card supports hot-swappable connectivity, allowing you to plug, unplug, and swap your FireWire peripherals with ease, saving time and hassle.

The 4 port FireWire PCI adapter card includes a copy of ULEAD's VideoStudio SE Basic video editing software, making it easy to capture and edit video from your digital video camcorder.

Certifications, Reports and Compatibility



Applications

- Add a high-speed FireWire port to a desktop without any FireWire ports
- Connect a digital camera to a desktop with a PCI slot to download photos and video
- Connect a external FireWire hard drive or optical drive to a PCI-enabled system

Features

- 3 external, 1 shared internal FireWire400 port, with supported data transfer rates up to 400 Mbps
- Compliant with IEEE 1394a - 2000 as well as 1394-1995 standards
- Includes Video Editing kit: Ulead Video Studio SE and FireWire cable
- Plug-and-Play and hot-swap compatible

Hardware	Warranty	Lifetime
	Bus Type	PCI (5 Volt)
	Card Type	Standard Profile
	Chipset ID	VIA - VT6306
	Industry Standards	IEEE 1394-1995
		IEEE 1394a
	OHCI	
	PCI 2.1	
	Interface	FireWire 400 (1394a)
	Ports	4
Performance	Maximum Data Transfer Rate	400 Mbps
Connector(s)	Connector Type(s)	1 - PCI (5V, 32-bit) Male
	External Ports	3 - FireWire 400 (6 pin, IEEE 1394a) Female
	Internal Ports	1 - FireWire 400 (6 pin, IEEE 1394a) Female
Software	Microsoft WHQL Certified	Yes
	OS Compatibility	Windows® 2000, XP®, Vista®, 7, 8, 8.1, 10 Windows Server® 2003, 2008 R2, 2012, 2012 R2, 2016 Mac OS® 8.6 to 10.4 Linux 2.6 to 4.4.x (LTS Versions Only)
Special Notes / Requirements	Note	The internal port and the top external port cannot be used at the same time. Only one or the other is active at a time.
	System and Cable Requirements	Unused PCI slot
Physical Characteristics	Product Height	3.1 in [8 cm]
	Product Length	4.7 in [12 cm]
	Product Weight	2.6 oz [75 g]
	Product Width	0.7 in [18 mm]
Packaging Information	Shipping (Package) Weight	0.6 lb [0.3 kg]
What's in the Box	Included in Package	1 - PCI Firewire Card
		1 - Firewire cable 4pin-6pin
		1 - Driver and Software CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.