

1 Port Low Profile PCI 10/100 Mbps Ethernet Network Adapter Card

Product ID: ST100SLP



This 1 Port PCI Fast Ethernet Network Adapter Card offers a reliable, cost-effective Ethernet network connection that's ideal for small form factor computers.

Delivering a simple connection to 10/100Mbps (Fast) Ethernet networks, the NIC features auto-negotiation that senses speed and duplex capabilities of connected devices and full duplex support for data transfer rates up to 200Mbps.

A versatile network interface solution, the NIC features a low profile mounting bracket that's suitable for small form factor computers, and is supported by all popular operating systems including Windows, Linux, Mac OS and Novell platforms. Backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- Replace a failed Ethernet port in a small form factor computer
- Add networking capabilities to an old system with no Ethernet port
- Add an additional Ethernet port to a desktop or workstation computer for redundancy

Features

- A single 10/100 Mbps compatible RJ45 Ethernet port
- Network Link/Activity and 10/100 Mbps LED indicators
- Fully Compliant with IEEE 802.3, IEEE 802.3u, IEEE 802.3x
- Full and half duplex support
- Crossover Detection & Auto-Correction (Auto MDI/MDI-X)
- Supports optional Boot ROM (Realtek RTL8139D Compatible Boot ROM required)

Hardware	Warranty	Lifetime
	Bus Type	PCI / PCI-X (5 / 3.3V)
	Card Type	Low Profile (SP bracket incl.)
	Chipset ID	Realtek - RTL8100C
	Industry Standards	IEEE 802.3/802.3u
	Interface	RJ45 (10/100 Ethernet)
	Ports	1
Performance	Compatible Networks	10/100 Mbps
	Full Duplex Support	Yes
	Maximum Data Transfer Rate	200 Mbits/Sec
Connector(s)	Connector Type(s)	1 - PCI / PCI-X (Universal 3.3 & 5V, 32-bit) Male
	External Ports	1 - RJ-45 Female
Software	OS Compatibility	Windows® NT, 98SE, 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server® 2008 R2, 2012, 2016 Mac OS® 10.0.4, 9.1 / 9.0 Unix, Linux 2.6 to 4.11.x <i>LTS Versions Only</i> NetWare 3.x/4.x
Special Notes / Requirements	Note	IRQ Line and I/O Address Assigned by system
Indicators	LED Indicators	1 - 10/100Mbps selection 1 - Network link/activity
Environmental	Humidity	10~90% RH Non-condensing
	Operating Temperature	0°C to 55°C (32°F to 131°F)
Physical Characteristics	Product Height	3.1 in [80 mm]
	Product Length	4.7 in [120 mm]
	Product Weight	1.5 oz [42 g]
	Product Width	0.8 in [20 mm]
Packaging Information	Shipping (Package) Weight	4.7 oz [132 g]
What's in the Box	Included in Package	1 - Low Profile 10/100 Mbps Ethernet PCI Card 1 - Full Profile bracket 1 - Driver CD 1 - Instruction Manual

Product appearance and specifications are subject to change without notice.