

2 Port VGA Auto Switch

Product ID: ST122VGAU



The ST122VGAU VGA Auto Switcher lets you share a display between two computers and prioritize your VGA signals. The VGA switch features a primary and secondary VGA input port, and automatically outputs the signal from the primary input. When the signal feed connected to the primary input port is cut, the switcher automatically defaults to the video signal on the secondary VGA input port.

Designed for maximum control and versatility, the VGA Auto switcher also offers manual control of connected signals with easy-to-use front panel buttons that allow you to toggle between video sources.

Certifications, Reports and Compatibility



Applications

- Ideal for use with a laptop computer and a boardroom projector in meetings and presentations, backup safety control systems, and home A/V switching applications
- Perfect for digital signage applications in retail environments requiring more than one media player or PC to be connected
- Great for connecting/switching multiple sources in Test Bench Facilities, Data Centers, Help Desks and Video Broadcasting Facilities

Features

- Automatically selects the priority of incoming video signals for display
- Supports resolutions up to 1920x1440
- Easy to use front panel selection buttons
- Easy installation - set up in minutes
- Video Bandwidth 250 MHz
- Rugged steel enclosure
- Supports DDC1, DDC2, DDC2B, DDC2B+, DDC2AB on port 1

Hardware	Warranty	2 Years
	Audio	No
	AV Input	VGA
	AV Output	VGA
	Industry Standards	DDC1, DDC2, DDC2B, DDC2B+, DDC2AB (DDC Support on Port 1 only)
	Ports	2
Performance	Bandwidth	250 MHz
	MTBF	80,000 hours
	Wide Screen Supported	Yes
Connector(s)	Connector A	2 - VGA (15 pin, High Density D-Sub) Female
	Connector B	1 - VGA (15 pin, High Density D-Sub) Female
Special Notes / Requirements	Note	Port 1 is set to have higher priority than port 2 when both signals are on
Power	Center Tip Polarity	Positive
	Output Current	0.3A
	Output Voltage	9 DC
	Power Consumption (In Watts)	2.7
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Height	7.7 in [195 mm]
	Product Length	5.1 in [130 mm]
	Product Weight	14.8 oz [419 g]
	Product Width	2.2 in [56 mm]
Packaging Information	Shipping (Package) Weight	25.8 oz [732 g]
What's in the Box	Included in Package	1 - 2 Port VGA Auto Switch
		1 - Universal Power Adapter (US/UK/EU/AUS)
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.