

## 3-Port Portable USB 3.0 Hub plus Gigabit Ethernet - Built-In Cable

Product ID: ST3300G3UA



Here's a must-have accessory for your MacBook. This portable USB 3.0 hub merges your USB peripheral and RJ45 network connections into a single, convenient combination hub. It gives you two vital connection types that are often missing from modern, port-limited laptops.

This silver, sandblasted USB hub matches the finish of your MacBook, and because it features a solid-aluminum casing that's both lightweight and rugged, it's perfect for travel usage. It also integrates a lengthier, 27 cm (10.5 in) cable, so you have the flexibility to place the hub, your devices, and your network connection, exactly where you need them.

### Looks great while expanding your connectivity

This high-quality, Apple style USB hub features a Gigabit Ethernet port, giving you an easy way to expand your MacBook connectivity. And because the hub integrates a Gigabit Ethernet port, you can add wired network connectivity to your laptop in a location where Wi-Fi® is unreliable or unavailable.

The hub's built-in USB cable has sufficient length to reach your laptop's USB 3.0 port, regardless of where the port is located.

Plus, the stylish hub features three USB 3.0 (also known as USB 3.1 Gen 1) ports in a compact housing. And, its silver, sandblasted finish provides a unique and trendy look when compared to traditional hubs.

### **Portable and rugged**

The hub features a rugged yet lightweight housing, so there's no need to sacrifice dependability for portability. With its compact, USB-powered design and a built-in USB cable, you can tuck the combination hub neatly into your travel bag, and avoid the nuisance of carrying multiple separate adapters.

This USB 3.0 hub is perfect for travel, such as back-and-forth trips from home to office. Plus, the compact hub takes up minimal space on a desk, so you can use it in hot-desk or BYOD (Bring Your Own Device) environments.

### **Save money and time**

This bus-powered USB hub installs quickly and easily, and it's natively supported in Windows®, Mac, and Chrome OS™, with no additional drivers or software required. You can also avoid the nuisance and cost of purchasing new devices by using the USB 3.0 hub plus GbE with your current USB 2.0 and 1.x devices.

The ST3300G3UA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect to a wired, Gigabit network where Wi-Fi is limited or unavailable, such as in boardrooms, classrooms, or hotels
- Add extra USB 3.0 ports and connect your peripherals at home, in the office, or while traveling
- Look trendy and contemporary, and upgrade the connection capabilities of your MacBook, Ultrabook, or laptop

### Features

- Sleek and stylish, with a silver, sandblasted finish that matches your MacBook
- Provides three USB 3.0 ports, and one Gigabit Ethernet port in a rugged, aluminum housing
- Travel friendly, with a portable, lightweight design and a built-in, extended-length cable that offers flexible desk placement options
- USB powered, so you can carry the hub with you anywhere
- Multi-platform compatibility with no drivers required, supports Windows, Mac, and Chrome OS
- Backward compatibility lets you save money and use with existing USB 2.0 and 1.x devices
- Dongle-style combination hub provides three SuperSpeed USB 3.0 ports, with throughput support up to 5Gbps
- Supports Wake-On-LAN, Energy-Efficient Ethernet, jumbo frames, full duplex flow control, VLAN tagging, and layer 2 priority encoding
- Provides overcurrent protection

<b>Hardware</b>	Warranty	2 Years	
	Bus Type	USB 3.0	
	Chipset ID	Genesys Logic - GL3520 Realtek - RTL8153	
	Fast-Charge Port(s)	No	
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab  IEEE 802.3az Energy-Efficient Ethernet, IEEE 802.3x Flow Control, 802.1q VLAN Tagging, 802.1p Layer 2 Priority Encoding  USB 3.0 - Backward compatible with USB 2.0 and 1.1	
	Interface	USB 3.0  USB 3.1 Gen 1  RJ45 (Gigabit Ethernet)	
	Ports	3	
	USB-C Device Port(s)	No	
	USB-C Host Connection	No	
	<b>Performance</b>	Auto MDIX	Yes
		Auto-Negotiation	Yes
		Compatible Networks	10/100/1000 Mbps
Flow Control		Full duplex flow control	
Full Duplex Support		Yes	
Jumbo Frame Support		9K max.	
Maximum Data Transfer Rate		5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
Type and Rate		USB 3.0 - 5 Gbit/s	
<b>Connector(s)</b>	Connector Type(s)	3 - USB Type-A (9 pin) USB 3.0 Female  1 - RJ-45 Female  1 - USB Type-A (9 pin) USB 3.0 Male	
	<b>Software</b>	OS Compatibility	
		Windows® 7, 8, 8.1, 10 Windows Server® 2008 R2, 2012, 2016 Mac OS® 10.7 to 10.14 Chrome OS™	
<b>Special Notes / Requirements</b>	<b>Note</b>	If connected to a USB 2.0 host port, performance may be limited	
	System and Cable Requirements	Host computer with a USB 3.0 port	

<b>Indicators</b>	LED Indicators	1 - Power 1 - Link/Activity (Network)
	<b>Power</b>	Power Source USB-Powered
<b>Environmental</b>	Humidity	10%~90% RH (Non-condensing)
	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-10°C to 70°C (14°F to 158°F)
<b>Physical Characteristics</b>	Cable Length	10.6 in [268 mm]
	Color	Silver & White
	Enclosure Type	Aluminum and Plastic
	Form Factor	Compact
	Product Height	0.7 in [18 mm]
	Product Length	4.3 in [110 mm]
	Product Weight	2.6 oz [73 g]
	Product Width	1.3 in [34 mm]
<b>Packaging Information</b>	Shipping (Package) Weight	5.2 oz [148 g]
<b>What's in the Box</b>	Included in Package	1 - 3-port USB 3.0 hub plus Gigabit Ethernet

Product appearance and specifications are subject to change without notice.