

8-Port Charging Station for USB Devices - 96W/19.2A

Product ID: ST8CU824



This USB charging station offers a high-powered solution for keeping your mobile devices powered and ready for use. It's compatible with a wide range of tablets and smartphones, and features built-in safety measures to help protect against damage to your mobile devices.

High-powered charging

The charging station can deliver 96 watts of power in total, providing 2.4 amps of power per port. That means you can charge eight tablets at once, and every port can provide the power each device needs.

One charger for all of your mobile devices

The charger supports USB Battery Charging Specification 1.2, which ensures compatibility with a broad range of mobile devices, including the Apple iPhone and iPad, the Microsoft® Surface™ tablet, the Samsung Galaxy Tab™, Android™ devices and more.

Dedicated charging

This all-in-one charger is perfect for charging multiple devices during meetings in a boardroom or conference room. It gives you and your co-workers access to charging when it's needed. Plus, consolidating your USB devices onto a single multi-port USB charger offers a more efficient solution and saves space because you don't need to use multiple wall outlets or power bars.

The compact, metal enclosure is extremely durable and offers simple operation using an integrated on/off power button that turns all ports on and off. For further flexibility, the charge station includes a bracket for wall-mounted installations.

Protection for your devices

The USB charging station features built-in safety measures to ensure that all of your devices are protected against damage from overheating, overvoltage, overcurrent or short circuiting. If the 96-watt limit is exceeded, the power being sent to the connected devices will turn off and the charger will reset itself until the load is reduced to safe levels. Plus, the charging station includes an internal fan which controls the temperature of the device in order to prevent overheating. The fan is automatically controlled to reduce noise levels.

The charger also includes an LED indicator beside each port to notify you of a short circuit, while the affected port will shut down until you power-cycle the charger.

The ST8CU824 is backed by StarTech.com's 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Charge up to eight mobile devices at once
- Use in IT helpdesk or tech-bench environments to charge multiple tablets, smartphones or other USB devices simultaneously
- Charge and deploy a fleet of tablets for mobile sales staff
- Set up a USB charging station at home for the whole family
- Install in locations where USB ports need to be securely mounted to a surface, such as a wall or on a desk

Features

- Charge almost any mobile device with USB Battery Charging Specification 1.2 support
- Deliver the fastest possible power output required for each connected device, up to a total of 96 watts (19.2 amps) shared between all eight ports
- Save space and wall outlets, using a single, consolidated charging station

Hardware	Warranty	2 Years
	Industry Standards	USB Battery Charging Specification Rev. 1.2
	Ports	8
Connector(s)	Connector Type(s)	8 - USB Type-A (4 pin) USB 2.0 Female
Indicators	LED Indicators	1 - Power 8 - Short circuit fault indicator beside each port
Power	Input Current	2A
	Input Voltage	100 ~ 240 AC
	Output Current	8A
	Output Voltage	12 DC
	Plug Type	M
	Power Consumption (In Watts)	96
	Power Source	AC Adapter Included
Environmental	Humidity	20~80% RH
	Operating Temperature	5°C to 35°C (41°F to 95°F)
	Storage Temperature	-20°C to 50°C (-4°F to 122°F)
Physical Characteristics	Color	Black
	Enclosure Type	Aluminum
	Product Height	1 in [25 mm]
	Product Length	8.3 in [212 mm]
	Product Weight	9.6 oz [272 g]
	Product Width	2.4 in [60 mm]
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	2.2 lb [1 kg]
What's in the Box	Included in Package	1 - USB Charging Station 2 - Wall-Mount Brackets 1 - Power Adapter 2 - Rubber Feet 4 - Mounting Screws

Product appearance and specifications are subject to change without notice.