

DC Power Adapter - 12V, 6.5A

Product ID: SVA12DN4NEUA



This replacement power adapter can provide a power source for any electronic device that has a 4-pin DIN barrel and requires 12 volts and up to 6.5 amps of power.

Replace your failed or lost power adapter

The adapter is a perfect replacement for the lost or damaged power adapter you've used to power your existing electronics.

Keep a spare power adapter on hand

When downtime isn't an option, keeping spare power adapters on hand ensures that you won't be left waiting for a replacement to arrive or have to replace your devices just for the sake of a compatible power source.

This power adapter is a direct replacement for the power adapters included with the following StarTech.com products:

[USB 3.0 / eSATA 4-Bay 3.5in SATA III Hard Drive Enclosure \(S3540BU33E\)](#)

[1U Rackmount 4-Bay 3.5in SATA / SAS External Hard Drive Enclosure \(SAT35401U\)](#)

[4 Bay eSATA USB 3.0 to SATA Hard Drive Docking Station \(SATDOCK4U3E\)](#)

[4 Bay USB 3.0 eSATA to SATA Standalone 1:3 HDD Hard Drive Duplicator Dock \(SATDOCK4U3RE\)](#)

[USB 3.0 to 4-Bay SATA 6Gbps Hard Drive Docking Station \(SDOCK4U33\)](#)

The SVA12DN4NEUA is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Replace a lost or broken power adapter
- Keep an extra power adapter on hand for your mission-critical devices
- Use a single power adapter as you travel between multiple regions

Features

- Supports a range of devices that require 12 volt and 6.5 amps (or less) of power and a DIN-type barrel connector
- Reduces downtime in the event of a failure, by keeping a spare power adapter on-hand

Power	Warranty	2 Years
	Input Voltage	100 ~ 240 AC
	Output Current	6.5 A
	Output Voltage	12 DC
	Plug Type	4-pin DIN
	Power Consumption (In Watts)	78
	Power Source	AC Adapter Included
Environmental	Humidity	0% - 80 % RH
	Operating Temperature	0°C to 60°C (32°F to 140°F)
	Storage Temperature	0°C to 60°C (32°F to 140°F)
Physical Characteristics	Product Height	1.3 in [34 mm]
	Product Length	5.1 in [130 mm]
	Product Weight	13.3 oz [378 g]
	Product Width	2.2 in [57 mm]
Packaging Information	Shipping (Package) Weight	2.2 lb [1 kg]
What's in the Box	Included in Package	1 - universal power adapter (NA/JP, EU, UK, AU)
	On-Screen Display	No

Product appearance and specifications are subject to change without notice.