

Universal VESA LCD Monitor Mounting Bracket for 19in Rack or Cabinet

Product ID: RKLcdbk



The RKLcdbk Universal VESA LCD Monitor Mounting Bracket for 19in Rack or Cabinet lets you mount almost any retail LCD or Touch screen panel into a server/storage rack/cabinet. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The LCD mounting bracket is made of solid cold pressed steel (SPCC), is designed to support 100mm and 75mm VESA mounted LCD panels, and meets ANSI/EIA RS-310-D standards rack mounting. A unique adjustable design enables an LCD panel to be mounted into the cabinet at various depths - allowing the rack/cabinet door to be closed.

The LCD mounting bracket also supports wall-mounted LCD installation, by inverting the adjustable bracket or by adding this bracket to a wall mount bracket or rack, such as the 6U (10 inch) Wallmount Bracket for 19" Rack Equipment (WALLMOUNT6) or 8U Open Frame Wall Mount Equipment Rack (RK812WALLO).

Backed by a StarTech.com Lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Ideal for installing a retail LCD monitor into an existing Rack or Cabinet solution
- Use for uptime/process monitoring with big screens over 19" when mounted outwards
- Adding a monitoring display to a security rack or cabinet
- Installing a touch screen display into a rack or cabinet
- Mounting an LCD monitor or TV to the wall

Features

- Adjustable 100mm and 75mm VESA mounting hole pattern for greater compatibility and control
- Adjustable depth between 0 to 3.5 inches
- TAA compliant for GSA Schedule purchases
- Meets ANSI/EIA RS-310-D standards
- Constructed from solid steel at 2.0mm thick, this bracket is designed for durability

Hardware	Warranty	Lifetime
	Cable Management	No
	Frame Type	Steel
	Industry Standards	EIA RS310-D
	U Height	4U
Physical Characteristics	Color	Black
	Internal Width	17.3 in [438.9 mm]
	Maximum Mounting Depth	3.5 in [88.9 mm]
	Minimum Mounting Depth	0 in [0 mm]
	Weight of Product	3.7 lb [1.7 kg]
Packaging Information	Package Height	8.7 in [22 cm]
	Package Length	18.6 in [47.2 cm]
	Package Width	2.1 in [54 mm]
	Shipping (Package) Weight	4.3 lb [2 kg]
What's in the Box	Included in Package	<ul style="list-style-type: none"> 2 - mounting brackets 1 - LCD bracket 8 - M5 cage nuts 8 - M5 screws 4 - M4 x 10mm LCD mounting screws 4 - M5 x 10mm bracket screws 4 - washers 1 - instruction manual

Product appearance and specifications are subject to change without notice.