

## 10m USB 2.0 Active Extension Cable - M/F

Product ID: USB2AAEXT10M



The USB2AAEXT10M 10m Active USB 2.0 Extension Cable offers one USB-A male connector and one USB-A female connector, and provides an active extension of USB 2.0 devices of up to 10-meters (30-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables.

Up to 4 of these cables can be daisy-chained together, allowing for a total USB extension of up to 40-meters. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT10M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain up to 4 cables together for even longer USB extensions

### Features

- 1x USB-A male connector
- 1x USB-A female connector
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows® 8/7/Vista/XP and Mac computer systems

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
<b>Connector(s)</b>	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Type-A (4 pin) USB 2.0 Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Cascade up to 4 USB2AAEXT10M devices together for further extension
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.35 A
	Input Voltage	110V-240V AC
	Output Current	1A
	Output Voltage	5 DC
	Plug Type	H
	Power Consumption (In Watts)	5
	Power Source	AC Adapter Included
<b>Physical Characteristics</b>	Cable Length	32.8 ft [10 m]
	Color	Black
	Connector Style	Straight
	Product Length	32.8 ft [10 m]
	Product Weight	14.5 oz [410 g]
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	23.9 oz [677 g]
<b>What's in the Box</b>	Included in Package	1 - 10m USB 2.0 Active Extension Cable - M/F
		1 - Universal Power Adapter
		1 - Plug Adapters for North America, UK, Europe, and Australia

Product appearance and specifications are subject to change without notice.