

5m Cisco Compatible SFP+ 10-Gigabit Ethernet (10GbE) Passive Twinax Direct Attach Cable

Product ID: SFPCMM5M



The SFPCMM5M Cisco Compatible 5m SFP+ cable is a fully hot pluggable, direct attach cable, supporting 10 Gigabit Ethernet and Fiber Channel applications connected through (Small Form Factor Pluggable) SFP+ ports.

Designed for short length, high speed interconnects, this low power, low latency Twinax cable is a cost-effective alternative to fiber optic cable assemblies and is intended for short distance applications such as point-to-point in-rack and across rack network switch/server connections.

Backed by our 2-year warranty, this 10GBASE-CU SFP+ Cable is compliant with MSA (Multi-Source Agreement) standards, making it a reliable replacement SFP-H10GB-CU5M cable.

Certifications, Reports and Compatibility



Applications

- Use in 10Gb Ethernet and Fiber Channel applications
- Point-to-point in-rack and across rack network switch/server connections (Storage Area Networks (SAN), Network Attached Storage (NAS), Storage Servers, etc.)

Features

- Compatible with Cisco equipment
- Compliant with SFP+ MSA Multi-Source Agreement standards
- Support for 1x, 2x, 4x and 8x Fiber Channel data rates
- Compliant with SFF 8431 connector standards
- 24AWG, 100 Ohm impedance
- Support for multi-gigabit data rates up to 10.5Gbps
- Hot-swappable with fiber optic modules
- Low Power consumption <0.5W
- Quick release latching SFP+ connectors

	Warranty	2 Years
Hardware	Cable Jacket Type	PVC - Polyvinyl Chloride
Performance	Compatible Networks	10 Gbps
	Impedance	100 Ohm
Environmental	Operating Temperature	0°C to 70°C
	Storage Temperature	-40°C to 80°C
Physical Characteristics	Cable Length	16.4 ft [5 m]
	Product Height	0.5 in [12 mm]
	Product Length	16.4 ft [5 m]
	Product Weight	11.2 oz [316 g]
	Product Width	0.6 in [14 mm]
	Wire Gauge	24 AWG
Packaging Information	Package Quantity	1
	Shipping (Package) Weight	11.5 oz [326 g]
What's in the Box	Included in Package	1 - 5m SFP+ 10-Gigabit Ethernet (10GbE) Twinax Cable
	Compatible Brand	Cisco
	Connector A	1 - SFP+ Latching Plug
	Connector B	1 - SFP+ Latching Plug

Product appearance and specifications are subject to change without notice.