

USB-C to USB-C Cable - M/M - 1 m (3 ft.) - USB 3.0 (5Gbps)

Product ID: USB315CC1M



This USB 3.0 USB-C™ to USB-C cable lets you connect a USB 3.0, USB Type-C™ device, such as a hard drive or mobile device, to the USB-C port on your computer, or charger. The cable is also compatible with Thunderbolt™ 3 ports.

Charge and sync your USB Type-C mobile devices

Connect your newer USB-C mobile devices, such as the Samsung Galaxy S8, S8+, Nexus™ 6P, and 5X phones, to your computer. The cable delivers up to a 3 amp (60W) charge, and supports data transfer speeds of up to 5Gbps.

Power your laptop

With up to 3A of power output, you can also use the USB Type-C cable to power a USB-C laptop, such as your Apple MacBook or Chromebook Pixel™. Simply connect your laptop to your USB-C wall charger.

Deliver full 4K video

The cable supports full 4K 60Hz video and DisplayPort 1.2 and is compatible with existing DisplayPort displays. It's ideal for connecting your docking station or laptop to a monitor with astonishing resolution, contrast, and color depth for amazing detail.

Connect your USB 3.0 peripherals

You'll also be able to connect your USB 3.0 peripheral devices, such as hard drive enclosures and docks, to your laptop.

The USB315CC1M from StarTech.com comes with a 2-year warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect a USB 3.0 device such as a portable hard drive or docking station to a USB-C laptop or desktop computer
- Charge and sync your USB-C mobile digital devices with your computer
- Charge your USB-C devices with a wall charger, car charger or power bank
- Power your USB-C enabled laptops with a USB Type-C wall charger

Features

- Supports data transfer rates up to 5Gbps
- Thunderbolt 3 port compatible
- Guaranteed reliability with our 2-year warranty

Hardware	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
Performance	Maximum Analog Resolutions	4K @ 60Hz
	Type and Rate	USB 3.1 Gen 1 - 5 Gbit/s
Connector(s)	Connector A	1 - USB Type-C (24 pin) USB 3.0 Male
	Connector B	1 - USB Type-C (24 pin) USB 3.0 Male
Power	Power Delivery	60W
Physical Characteristics	Cable Length	3.3 ft [1 m]
	Color	Black
	Connector Style	Straight
	Product Height	0.2 in [5 mm]
	Product Length	3.3 ft [1 m]
	Product Weight	1.4 oz [40 g]
	Product Width	0.5 in [12 mm]
	Wire Gauge	24/32 AWG
Packaging Information	Shipping (Package) Weight	1.6 oz [46 g]
What's in the Box	Included in Package	1 - USB-C cable

Product appearance and specifications are subject to change without notice.