

## 3m USB 3.0 Active Extension Cable - M/F

Product ID: USB3AAEXT3M



The USB3AAEXT3M, 3-meter Active USB 3.0 Extension Cable, offers one USB type-A (male) connector and one USB type-A (female) connector, and provides an active extension of USB 3.0 devices of up to 3-meters (10-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations; the active USB 3.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the typical length limits of standard USB cables. Up to 4 of these cables can be daisy-chained together, allowing the connection to be extended a total of 12-meters. If necessary, the USB device can be powered from a wall outlet, using the Universal AC power adapter provided with the cable.

The USB3AAEXT3M extension cable (USB Extender) supports high speed USB 3.0 transfer rates of up to 5Gbps, and is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the distance of USB peripherals beyond the USB 3.0 3-meter limitation
- Cascade up to 4 levels
- Backwards compatible with USB 2.0/1.1 devices

### Features

- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring
- Compatible with PC Windows® 8/7/Vista/XP and Mac computer systems

<b>Hårdvara</b>	Warranty	2 Years
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kontaktplätering	Nickel
<b>Kontakt(er)</b>	Connector A	1 - USB Type-A (9-stifts) USB 3.0 Hane
	Connector B	1 - USB Type-A (9-stifts) USB 3.0 Hona
<b>Särskilda anmärkningar/krav</b>	<b>Obs.</b>	Cascade up to 4 USB3AAEXT3M devices together for further extension
<b>Ström</b>	Inspänning	110V-240V AC
	Inström	0.35 A
	Kontakttyp	H
	Polaritet på mittpol	Positiv
	Power Source	AC-adapter medföljer
	Strömförbrukning	10
	Utspänning	5 DC
	Utström	2A
<b>Utseende</b>	Färg	Svart
	Kabellängd	9.8 ft [3 m]
	Produktlängd	9.8 ft [3 m]
	Produktvikt	8.1 oz [230 g]
<b>Förpackning</b>	Förpackningsantal	1
	Fraktvikt (förpackning)	0.7 lb [0.3 kg]
<b>Vad det är i lådan</b>	Ingår i paketet	1 - 3 m USB 3.0 Active Extension Cable - M/F 1 - Universal Power Adapter 1 - Plug Adapters for North America, UK, Europe, and Australia

Product appearance and specifications are subject to change without notice.