

Travel Docking Station for Laptops - HDMI or VGA - USB 3.0

Product ID: USB3SMDOCKHV



The travel docking station for laptops lets you transform your laptop or Ultrabook™ into a mobile workstation. It adds HDMI® or VGA video output, a USB 3.0 hub port, and a Gigabit Ethernet RJ45 port, through a single USB 3.0 host connection. The travel-friendly dock helps you overcome the port limitations of modern mobile computers, making it ideal for your laptop, Microsoft Surface™ Pro 4, Surface Pro 3, Surface 3, Surface Pro 2 or Surface Book.

Now, you can avoid the nuisance of carrying multiple adapters. By consolidating four essential connection ports into one convenient device, the travel dock is the the perfect laptop accessory. It features a lightweight, compact design that fits nicely into your travel bag and also features an integrated host connection cable that tucks neatly into the docking stations casing.

A versatile solution for connecting an additional display to your laptop, the travel docking station offers HDMI video output with audio, or VGA video output, providing two popular interfaces for connecting a television, projector, or monitor as a second display, with support for resolutions up to 2048x1152 (QWXGA). Leveraging the high-bandwidth (5Gbps) USB 3.0 interface to deliver flexible video output, a USB 3.0 hub port, and Gigabit Ethernet, you can quickly set up a multi-functional workstation while on the run, without sacrificing one of your laptop USB ports.

Setup is seamless and hassle-free; the travel dock will automatically download the latest driver when connected to a Mac or Windows® system with an active network connection.

The USB3SMDOCKHV is backed by a StarTech.com 3-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Work from your Ultrabook or laptop easily, while you're on the run or on the road, by adding essential connectivity options
- Use your Ultrabook or laptop as a multi-display workstation, through external monitor support, and run multiple applications on different screens
- Use an HDMI port-equipped television in a hotel room as a second display when traveling
- Add an extra display as well as wired Gigabit network access to your slimline laptop, while keeping your USB 3.0 port available for other connections
- Connect to your HDMI or VGA-equipped projector and display multimedia content at home, or engaging presentations in boardrooms
- Connect your laptop to a wired Gigabit network in situations where a WiFi connection isn't available, such as in classrooms, offices, and hotels

Features

- HDMI® or VGA video output, USB 3.0 hub port, and GbE through just a single USB 3.0 connection
- Compact and lightweight - multiple connection options in a travel-friendly casing designed for maximum portability
- Built-in USB 3.0 cable, which can be tucked away neatly while not in use
- USB bus-powered - No external power adapter required
- Hassle-free setup - Latest drivers are automatically downloaded in Windows® systems when an active network connection is present
- Gigabit Ethernet RJ45 port - IEEE 802.3, 802.3u and 802.3ab (10BASE-T, 100BASE-TX, and 1000BASE-T) compatible
- SuperSpeed USB 3.0 (5 Gbps) interface, backward compatible with USB 2.0
- Support for resolutions up to 2048x1152 (QWXGA)
- Compatible with USB-enabled Mac and Windows laptops and Windows based tablets, such as the Microsoft Surface Pro 4 and Surface Book
- Choose between Mirrored, Extended or Primary display configurations

Hardware	Warranty	3 Years	
	4K Support	No	
	Bus Type	USB 3.0	
	Chipset ID	DisplayLink - DL-3700	
	Displays Supported	1	
	Fast-Charge Port(s)	No	
	Industry Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab USB 3.0 - Hub port supports USB 2.0/1.1 backward-compatibility	
Performance	Auto MDIX	Yes	
	Compatible Networks	10/100/1000 Mbps	
	Full Duplex Support	Yes	
	Maximum Analog Resolutions	2048x1152 (VGA) Lower resolutions are also supported.	
	Maximum Data Transfer Rate	5 Gbps (USB 3.0) 2 Gbps (Ethernet; Full-Duplex)	
	Maximum Digital Resolutions	2048x1152 (HDMI) Lower resolutions are also supported.	
	Type and Rate	USB 3.0 - 5 Gbit/s	
	UASP Support	Yes	
Connector(s)	Connector Type(s)	1 - USB Type-A (9 pin) USB 3.0 Male 1 - HDMI (19 pin) Female 1 - VGA (15 pin, High Density D-Sub) Female 1 - RJ-45 Female 1 - USB Type-A (9 pin) USB 3.0 Female	
	Software	OS Compatibility	Windows® XP SP3 (32-bit), Vista, 7, 8, 8.1, 10 macOS 10.6 - 10.12, 10.14
	Special Notes / Requirements	Note	Only a single video output can be used at one time, HDMI® or VGA. If a display is connected to each video output port at the same time, then the HDMI® port will take priority
		System and Cable Requirements	USB enabled computer system with available USB 3.0 port
	Indicators	LED Indicators	1 - Link (Green) 1 - Activity (Yellow)
Power		Power Source	USB-Powered
Environmental	Humidity	90% RH	

	Operating Temperature	0°C to 40°C (32°F to 104°F)
	Storage Temperature	-20°C to 70°C (-4°F to 158°F)
Physical Characteristics	Cable Length	3.7 in [93 mm]
	Color	Black
	Enclosure Type	Plastic
	Product Height	0.7 in [1.7 cm]
	Product Length	4.9 in [12.5 cm]
	Product Width	2.2 in [55 mm]
	Weight of Product	2.9 oz [82 g]
Packaging Information	Package Height	1.7 in [43 mm]
	Package Length	5.6 in [14.3 cm]
	Package Width	6.6 in [16.7 cm]
	Shipping (Package) Weight	6.8 oz [192 g]
What's in the Box	Included in Package	1 - USB 3.0 Mini Docking Station
		1 - Driver CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.