

## 0.5m Mini USB Cable - A to Up Angle Mini B

Product ID: USBAMB50CMU



The USBAMB50CMU 50cm USB to Up Angle Mini USB Cable provides a high quality connection between your Mini USB 2.0 mobile devices (smartphones, GPS, digital cameras, portable hard drives, etc.) and your PC or Mac® computer, for everyday tasks such as charging, data synchronization or file transfers.

The up-angled Mini USB connector allows you to access your Mini USB devices, while keeping the cable out of the way, and stress away from the port.

Perfect for close-range device connections, our shorter mini USB cables provide a portable solution that makes them perfect for carrying as an accessory for your tablet or laptop.

Designed and constructed for maximum durability, this high quality USB to Mini USB cable is backed by StarTech.com's Lifetime Warranty.

As an alternative, StarTech.com also offers a 0.5m USB to Down Angle Mini USB Cable (USBAMB50CMU), which provides the same convenience as this up-angled cable, but allows you to connect to your Mini USB device from the opposite direction.

### Certifications, Reports and Compatibility



### Applications

- Transfer data and provide power while charging your Mini USB device, without the cable getting in the way

### Features

- 1x USB 'A' male connector
- 1x Up Angle USB Mini-B male connector
- Supports high-speed data transfer rates of up to 480 Mbps
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief
- Offers 0.5m in cable length

|                           |                         |  |
|---------------------------|-------------------------|--|
| <b>Hårdvara</b>           | Warranty                | Lifetime                                       |
|                           | Kabelmanteltyp          | PVC - Polyvinyl Chloride                       |
|                           | Kabelskärmning          | Aluminiummylarfolie med flätning               |
|                           | Kontaktplätering        | Nickel   |
| <b>Prestanda</b>          | Typ och hastighet       | USB 2.0 - 480 Mbit/s                           |
| <b>Kontakt(er)</b>        | Connector A             | 1 - USB Type-A (4-stifts) USB 2.0 Hane         |
|                           | Connector B             | 1 - USB Mini-B (5-stifts) Hane                 |
| <b>Utseende</b>           | Färg                    | Svart  |
|                           | Kabellängd              | 1.6 ft [0.5 m]                                 |
|                           | Kontakttyp              | Rak till uppvinklad                            |
|                           | Produktbredd            | 0.6 in [16 mm]                                 |
|                           | Produkt höjd            | 0.8 in [20 mm]                                 |
|                           | Produktlängd            | 1.6 ft [0.5 m]                                 |
|                           | Produktvikt             | 0.7 oz [19 g]                                  |
|                           | Tråddimension           | 28 AWG   |
| <b>Förpackning</b>        | Förpackningsantal       | 1  |
|                           | Fraktvikt (förpackning) | 0.8 oz [24 g]                                  |
| <b>Vad det är i lådan</b> | Ingår i paketet         | 1 - 0.5m Mini USB Cable - A to Up Angle Mini B |

Product appearance and specifications are subject to change without notice.