

## 15m USB 2.0 Active Extension Cable - M/F

Product ID: USB2AAEXT15M



The USB2AAEXT15M 15m Active USB 2.0 Extension Cable, offers one USB 'A' male connector and one USB 'A' female connector, and provides an active extension of USB 2.0 devices of up to 15-meters (49.2-feet).

An all-in-one cable for overcoming distance restrictions as well as power source limitations, the active USB 2.0 extension cable incorporates bus-powered active circuitry to ensure performance beyond the length limits of standard USB cables.

Up to 4 of these cables can be daisy-chained together, allowing for a total USB extension of up to 60-meters. If necessary, the USB device can be powered from a wall outlet using the Universal AC power adapter (provided with the cable).

The USB2AAEXT15M repeater cable supports the full USB 2.0 bandwidth of 480 Mbps, and is backed by StarTech.com's 2-year Warranty.

### Certifications, Reports and Compatibility



### Applications

- Extend the distance of USB peripherals beyond the USB 2.0 5-meter limitation
- Daisy chain up to 4 cables together for even longer USB extensions

### Features

- 1x USB 'A' male connector
- 1x USB 'A' female connector
- Fully shielded for error-free connections
- Plug-and-play, no driver required
- USB bus-powered
- Universal external power source also included
- Blue LED indicator x1 for Extension Cable and USB port connection status monitoring

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
<b>Connector(s)</b>	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Type-A (4 pin) USB 2.0 Female
<b>Special Notes / Requirements</b>	<b>Note</b>	Cascade up to 4 USB2AAEXT15M devices together for further extension
<b>Power</b>	Center Tip Polarity	Positive
	Input Current	0.35 A
	Input Voltage	110V-240V AC
	Output Current	1A
	Output Voltage	5 DC
	Plug Type	H
	Power Consumption (In Watts)	5
	Power Source	AC Adapter Included
<b>Physical Characteristics</b>	Cable Length	49.2 ft [15 m]
	Color	Black
	Product Height	0.4 in [9 mm]
	Product Length	49.2 ft [15 m]
	Product Weight	21 oz [596 g]
	Product Width	0.6 in [16.5 mm]
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	30.6 oz [866 g]
<b>What's in the Box</b>	Included in Package	1 - 15m USB 2.0 Active Extension Cable - M/F 1 - Universal Power Adapter 1 - Plug Adapters for North America, UK, Europe, and Australia

Product appearance and specifications are subject to change without notice.