


# Long Micro-USB Charge-and-Sync Cable M/M - 24 AWG - 3 m (10 ft.)

Product ID: USBAUB3MBK



Tired of being attached to the wall when charging and using your phone or tablet?

The USBAUB3MBK Micro USB cable offers 3 meters in cable length so you can charge your device in comfort and from a distance. Plus, the cable offers a slim design that lets you plug into your device without having to take it out of its case for every charge and sync.

## Charge and work from a distance

Charge your device even while you're taking notes in a boardroom, catching up on emails in a hotel room, or reading in a coffee shop. The 3-meter long charge cable overcomes distance restrictions and lets you stay connected even while charging.

## **Deliver full charging power**

Provide full charging power, with no loss of charge time, even at distances of up to 10 feet (3 meters) away from your charger. The heavier gauge (24/30 AWG) wire lets you charge your mobile devices without slowing down charge time - allowing you to stay connected and charge at the same speed as you would using a shorter cable.

## **Connect with ease**

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a slim Micro USB connector molding that plugs into your device even while it's inside a protective case.

Designed and constructed for maximum durability, this high quality USB-A to Micro-B cable is backed by StarTech.com's Lifetime Warranty.

### Certifications, Reports and Compatibility



### Applications

- Charge and sync your Micro USB-equipped mobile digital devices

### Features

- Offers 3m in cable length
- Slim Micro USB connector molding
- Aluminum-mylar foil with braided shielding
- Supports high-speed USB data transfer rates of up to 480 Mbps

<b>Hardware</b>	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male
	Connector B	1 - USB Micro-B (5 pin) Male
<b>Special Notes / Requirements</b>	<b>Note</b>	Micro USB connector molding width is 10mm and height is 6mm (please see drawing)
<b>Physical Characteristics</b>	Cable Length	9.8 ft [3 m]
	Color	Black
	Connector Style	Straight
	Product Length	9.8 ft [3 m]
	Product Weight	2.2 oz [61.3 g]
	Wire Gauge	24/30 AWG
<b>Packaging Information</b>	Package Quantity	1
	Shipping (Package) Weight	2.2 oz [62.3 g]
<b>What's in the Box</b>	Included in Package	1 - 3m Mobile Charge Sync Micro USB Cable - A to Micro B

Product appearance and specifications are subject to change without notice.