

USB 3.0 to eSATA HDD / SSD / ODD Adapter Cable - 91cm eSATA Hard Drive to USB 3.0 Adapter Cable - SATA 6 Gbps

Product ID: USB3S2ESATA3



The USB3S2ESATA3 USB 3.0 to eSATA drive cable lets you connect any external eSATA hard drive, solid state drive, or optical disc drive to your USB-enabled computer system -- a great solution for computers that don't natively support eSATA, such as MacBook® and Ultrabook™ computers.

To maximize performance and utilize the speed potential of your SATA 6 Gbps drives, the USB 3.0 to eSATA adapter is compatible with SATA revisions I/II/III and supports transfer speeds up to 5 Gbps through USB 3.0.

With support for Blu-ray/DVD/CD ATAPI / ODD drives and large capacity HDD / SSDs (tested up to 4TB) the USB to eSATA adapter cable is compatible with virtually any eSATA device, and can greatly increase the storage/backup capabilities of your computer.

The USB 3.0 to eSATA drive cable ensures a hassle-free connection with simple plug-and-play installation, plus the cable is the perfect length (1-meter, end-to-end) for easily accessing the rear panel USB ports on your computer.

The USB3S2ESATA3 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect an external eSATA drive to a computer system that only has USB
- Carry with your laptop and eSATA drive for an on the go storage solution
- Swap an eSATA drive between computers systems that do not have eSATA

Features

- Compatible with USB 3.0/2.0/1.1 (5 Gbps / 480 Mbps / 1.5 Mbps)
- eSATA interface compliant with SATA revision 3 and other SATA revisions, with supported data transfer rates up to 6 Gbps
- Supports hard drives (HDD), solid state drives (SSD) and optical disc drives (ODD)
- 1x eSATA connector, 1x USB 3.0 connector with integrated 1m (3.3ft) cable
- No driver or software installation required
- Plug-and-Play and Hot-Swap compatible

| | | |
|---------------------------------|----------------------------|--|
| Hardware | Warranty | 2 Years |
| | Bus Type | USB 3.0 |
| | Chipset ID | ASMedia - ASM1153E |
| | Compatible Drive Types | SATA |
| | Number of Drives | 1 |
| Performance | 4Kn Support | Yes |
| | Hot Swap Capability | Yes |
| | Max Drive Capacity | Currently tested with up to 4TB 7200 RPM hard drives |
| | Maximum Data Transfer Rate | 5 Gbps |
| | Port Multiplier | No |
| | Type and Rate | USB 3.0 - 5 Gbit/s SATA III (6 Gbps) |
| | UASP Support | No |
| Connector(s) | Drive Connectors | 1 - eSATA (7 pin, Data) Female |
| | Host Connectors | 1 - USB Type-A (9 pin) USB 3.0 Male |
| Software | OS Compatibility | OS independent; No software or drivers required |
| Environmental | Humidity | 40%-85%RH |
| | Operating Temperature | 0°C to 60°C (32°F to 140°F) |
| | Storage Temperature | -10°C to 70°C (14°F to 158°F) |
| Physical Characteristics | Product Height | 0.4 in [10 mm] |
| | Product Length | 35.8 in [910 mm] |
| | Product Weight | 2.4 oz [67.5 g] |
| | Product Width | 0.9 in [24 mm] |
| Packaging Information | Shipping (Package) Weight | 2.8 oz [80 g] |
| What's in the Box | Included in Package | 1 - USB 3.0 to eSATA Adapter Cable 1 - Installation guide |

Product appearance and specifications are subject to change without notice.