

Bulk Cat 6 Ethernet Cable - 1000 ft. - Solid - Plenum CMP - Gray

Product ID: WIRC6CMPGRY



The WIRC6CMPGRY Cat6 Plenum Bulk Cable (1000 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a foot-marked jacket that enables you to measure your cable runs to your exact installation requirements. Also, the gray PVC jacket enables you to color code your drops as needed for a more organized installation.

Constructed of only top quality materials, the WIRC6CMPGRY delivers reliable performance and is backed by our Lifetime Warranty.

Plenum Rated

This Category 6 cable has been tested for CMP (FT6) plenum-ratings, and is ideal for installation in air plenums, ducts, walls, conduit, ceilings, etc. where CMP fire rating is required.

100% Copper - a better value

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable, based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

23 AWG Wire

This Cat6 cable is constructed with 23 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

Certifications, Reports and Compatibility



Applications

- Can be used in air ducts and plenums where CMP fire rating is required
- Designed for use with Gigabit networks

Features

- UL Listed CMP/FT6 Plenum Fire Rating
- Foot-marked cable
- ETL Verified
- High quality 23 AWG copper wire
- Carefully constructed and tested, to keep Near End Crosstalk (NEXT) well within acceptable limits
- Constructed with top quality components

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Fire Rating	CMP Rated (Plenum)
Performance	Cable Rating	CAT6 - 500 MHz
Physical Characteristics	Cable Length	1000 ft [304.9 m]
	Color	Gray
	Conductor Type	Solid Copper
	Product Height	0.2 in [5 mm]
	Product Length	1000 ft [304.9 m]
	Product Weight	30 lb [13.6 kg]
	Product Width	0.2 in [5 mm]
	Wire Gauge	23 AWG
Packaging Information	Shipping (Package) Weight	32.7 lb [14.8 kg]
What's in the Box	Included in Package	1 - 1000 ft Roll of Gray Plenum CMP Cat 6 Solid UTP Bulk Cable

Product appearance and specifications are subject to change without notice.