


6 ft USB to Parallel Printer Adapter - M/M

StarTech ID: ICUSB1284



This USB to Parallel Interface Converter Cable allows PCs that support the USB specification to print to any standard parallel printer. The USB interface provides a much faster data transfer rate than a standard parallel port, thereby reducing the time waiting for a print job to be sent to your printer.

This portable device is self-powered and provides Plug and Play installation to any USB-compliant computer running Windows 98/ME/2000/XP/Vista.

Applications and Solutions

- Allows you to quickly add a parallel port to your Windows 98SE/ME/2000/XP computer

Features

- Fully Plug & Play for easy installation
- High speed bi-directional parallel port compliant to IEEE-1284 industry standard
- Low power consumption as it draws power from the USB connection
- No IRQ required for installation
- Supports Windows 98, Windows ME, Windows 2000/XP/Vista

Technical Specifications

- Connector Types: 1 - USB A Male
- Connector Types: 1 - Centronics 36 Male
- Product Length: 6.08 ft [1.85 m]
- Operating Temperature: 5 ~ 40
- Power Consumption: .90
- Carton Quantity: 50
- Storage Temperature: -20 ~ 70
- Shipping (Package) Weight: 0.33 lb [0.15 kg]
- Connectors: USB Type A Male, Centronics 36 Male
- Cable Length: 180cm (72 in.)
- Power Consumption: 90mA (max)
- Power Mode: Bus powered
- Operating Temperature: 5~40 deg C
- Storage Temperature: -20~60 deg C
- Humidity: 0~80% RH non-condensing
- Enclosure: Plastic
- Weight: 110g
- Certifications: FCC Part 15, CE Mark