

25 ft Coax High Resolution VGA Monitor Extension Cable - HD15 M/F

StarTech ID: MXT101HQ_25



This 25ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by 25ft, while maintaining superb image quality.

Applications and Solutions

- Connects PC's VGA port to a StarView
- Extends VGA/SVGA monitor cable

Features

- Ferrite core eliminates EMI interference
- Ideal for high resolution monitors (1024x768 and above)
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Molded connector ends with strain relief
- Triple-coaxial + twisted-pair wire for crystal clear display

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 20
- Shipping (Package) Weight: 2.06 lb [0.93 kg]
- Cable Length: 25 ft [7.62 m]
- Connector A: 1 - 15 pin High Density D-Sub (VGA) Male
- Connector B: 1 - 15 pin High Density D-Sub (VGA) Female

