

2 Port VGA Video Splitter - 250 MHz

StarTech ID: ST122L



This two Port VGA Video Splitter allows a computer to display VGA video from a single source on two monitors simultaneously.

Perfect for classrooms, tradeshow, or any environment requiring high quality video on several monitors, the VGA splitter supports displays with up to 250 MHz of bandwidth and up to 1920 x 1440 resolution. Plus, to simplify placement of your VGA displays, the splitter features a built-in booster circuit that allows you to locate VGA monitors up to 210ft away from your VGA signal source.

The ST122L VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- 250 MHz bandwidth provides brilliant resolutions up to 1920 x 1440 pixels
- Compatible with VGA, SVGA and Multisync monitors
- Daisy chainable up to three levels.

Technical Specifications

- Color: Black
- Enclosure Type: Steel
- Product Height: 1.02 in [25.91 mm]
- Input Current: 0.5
- Product Length: 2.56 in [65.02 mm]
- Number of Ports: 2
- Center Tip Polarity: Positive
- Carton Quantity: 10
- Shipping (Package) Weight: 1.86 lb [0.84 kg]
- Product Weight: 7.8 oz [221 g]
- Product Width: 5.16 in [131.06 mm]
- Video Input: 1 x HD-15 VGA Male Connectors
- Video Output: 2 x HD-15 VGA Female Connectors
- Video Bandwidth: 250 MHz
- Maximum Video Resolution: 1920 x 1440
- Maximum Cable Distance: 210 feet (65m)
- EDID Support: No