

2 Port High-Resolution 400 MHz VGA Video and Audio Splitter / Distribution Amplifier

StarTech ID: ST122PROA



Be seen and heard! StarTech.com's ST122PROA add audio to your multi-screen presentations. Now you can split video and audio from one computer between two sets of VGA displays and speakers. Great for classrooms, in-store merchandising, or information kiosks, the ST122PROA is a great way to make your presentation stand out in a crowd.

A built-in signal booster lets you place your displays up to 210 feet away from your computer while maintaining a crisp 2048 x 1536 VGA resolution. Plus, easy plug and play installation lets you take your show anywhere and set up in seconds. Backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- 400 MHz bandwidth provides brilliant 2048 x 1536 resolution
- Compatible with VGA, SVGA and Multisync monitors
- Daisy chainable for almost unlimited expansion
- DDC, DDC2 & DDC2B compatible (on Video Out port 1)
- Includes DC 7.5V power adapter
- Uses standard monitor extension cables (StarTech.com coaxial VGA cables recommended for best picture quality)

Technical Specifications

- Color: Gray
- Connector Types: 3 - High Density 15 pin Female
- Connector Types: 3 - Phono 3.5 mm Female
- Product Height: 2.83 in [7.2 cm]
- Product Length: 5.12 in [13 cm]
- Maximum Analog Resolutions: 2048 x 1536
- Number of Ports: 2
- Carton Quantity: 20
- Shipping (Package) Weight: 2.14 lb [0.97 kg]
- Product Width: 2.95 in [7.5 cm]
- Signal Type: XGA, VGA, SVGA, QXGA, UXGA and Multisync displays
- Cable Length: 210 feet (65 meters)
- Input Connectors: Video: 1 x High Density DB15 (Female), Audio: 1 x 3.5mm Audio Jack (Female)
- Output Connectors: Video: 2 x High Density DB15 (Female), Audio: 2 x 3.5mm Audio Jack (Female)
- VGA Bandwidth: 400 MHz
- VGA Resolution: 2046 x 1536 @ 60 Hz
- Dimensions: 5.1 x 2.9 x 1.6 Inches (130 x 75 x 72 mm)
- Power Adapter: AC 7.5V 800mA (max) (Up till August 2008)
- New Power Adapter: DC 12V, 600mA (After August 2008)