


## 1 Port PCI Dual Voltage Parallel Adapter Card

StarTech ID: PCI1PECPDV



This PCI Dual Voltage EPP/ECP Parallel Adapter Card adds an IEEE 1284 port to your PC, with support for data transfer speeds of up to 1.5 Mbps – up to 3 times faster than built-in parallel ports.

A versatile solution, the Parallel Adapter Card can be installed in either a PCI 5V or PCI-X 3.3v PCI slot, making installation simple.

The adapter card supports Windows® Vista™, XP, ME, 2000, 98SE, NT4, DOS® and Linux®. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

This PCI Parallel adapter card is a complete dual profile solution, providing both a standard bracket and a low profile bracket for adapting to slimline or small form factor system applications.

### Applications and Solutions

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

## Features

- Maximum data transfer rate of 1.5 Mbps
- PCI 2.2 and PCI Power Management 1.0 compliant
- SPP/EPP/ECP Parallel port that fully supports existing Centronics interface

## Technical Specifications

- Warranty: Lifetime warranty
- Bus Type: PCI / PCI-X (5 / 3.3V)
- Connector Types: 1 - DB25 Female
- Carton Quantity: 48
- Shipping (Package) Weight: 0.31 lb [0.14 kg]
- Bus Type: PCI 5V / PCI-X 3.3V
- Maximum Data Transfer Rate: 1.5 Mbps
- Compatible OS: Windows 95, 98, ME; Windows XP (32-bit, 64-bit), Windows Vista (32-bit, 64-bit), Linux 2.4.x and up
- Chipset: Oxford OX16PCI1952

