

4 Port Selectable Output High-Resolution 400 MHz VGA Video Splitter / Distribution Amplifier

StarTech ID: ST124SW



Add life to your multi-screen presentations! StarTech.com's VGA splitter/selector lets you share and control your computer's VGA signals to up to four displays. The ST124SW lets you turn the signal to each device on or off with just the push of a button, making for more dramatic, eye-catching presentations.

A built-in signal booster lets you place your monitors up to 246 feet away from your computer while maintaining high-quality VGA resolution. Easy install and set-up provides the perfect solution for permanent and mobile presentations.

Applications and Solutions

- Demos and presentations
- In-store product merchandising
- Information kiosks
- Public broadcast systems

Features

- Allows one computer to provide simultaneous display on four different monitors
- Built-in video amplifier boosts the signal to allow a cable length of up to 246 ft. or 75 meters
- Daisy chainable for almost unlimited expansion
- Easy Plug & Play installation
- Port selection switch lets you switch from one monitor to four monitors
- Works with VGA, SVGA and Multisync monitors

Technical Specifications

- Color: Gray
- Connector Types: 4 - High Density 15 pin Female
- Connector Types: 1 - High Density 15 pin Male
- Product Height: 1.77 in [45 mm]
- Input Current: 0.3
- Input Voltage: 9
- Product Length: 5.71 in [145 mm]
- Maximum Analog Resolutions: 2048 x 1536
- Carton Quantity: 20
- Shipping (Package) Weight: 2.14 lb [0.97 kg]
- Product Weight: 16.81 oz [476.2 g]
- Product Width: 3.94 in [10 cm]
- Connectors:
- Input Connectors: 1 x High Density DB15 Male
- Output Connectors: 4 x High Density DB15 Female
- Compatibility: VGA, SVGA, XGA & Multisync displays
- Max Resolution: 2048 x 1536 pixels
- Video Bandwidth: 400 MHz
- Frequency:
- Horizontal: 30 - 100 KHz
- Vertical: 43 - 120 MHz
- Cable distance:
- Computer to Switch: 25 Feet (7.5 meters)
- Switch to display: 246 Feet (75 meters)
- LED Indicators: 1 x Power
- Port Selection: Local Monitor & Local/Remote Monitor
- Enclosure: Metal case

- Power: 9V DC (300Ma)
- Dimensions: 5.7 x 3.9 x 1.6 inches (145 x 100 x 40 mm)