

8 Port VGA Video Splitter - 250 MHz

StarTech ID: ST128L



This 8-port VGA splitter/distribution amplifier allows a computer to display VGA video on up to eight monitors simultaneously, with no loss of video quality.

Providing support for up to **250 MHz** of video bandwidth, the eight port VGA Video Splitter provides brilliant **1920x1440** resolution and features a built-in booster circuit that allows you to locate VGA displays up to **210 ft** away from the signal source.

Plus, the video splitter provides easy plug and play installation that lets you take your show anywhere and set up in seconds!

The **ST128L VGA Video Splitter / Distribution Amplifier** is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Trade-shows

Features

- 250 MHz bandwidth provides brilliant resolutions up to 1920 x 1440 pixels
- Compatible with VGA, SVGA and Multisync monitors
- Daisy chainable up to three levels.

Technical Specifications

- Warranty: 1 Year warranty
- Color: Black
- Product Height: 1.02 in [25.91 mm]
- Product Length: 2.56 in [65.02 mm]
- Number of Ports: 8
- Carton Quantity: 10
- Shipping (Package) Weight: 2.52 lb [1.14 kg]
- Product Weight: 7.8 oz [221 g]
- Product Width: 5.16 in [131.06 mm]
- Video Input: 1 x HD-15 VGA Male
- Video Output: 8 x HD-15 VGA Female Connectors
- Video Bandwidth: 250 MHz
- Maximum Video Resolution: 1920 x 1440
- Maximum Cable Distance: 210 feet (65m)
- Input Current: 0.5A
- Power Adapter: DC 9V 500mA Type M connector
- EDID Support: No

