

2 Port VGA Video Splitter - 300 MHz

StarTech ID: ST122LE



This two Port VGA Video Splitter allows a computer to display VGA video on two monitors simultaneously.

Perfect for classrooms, tradeshow, or any environment requiring high quality video on several monitors, the ST122LE VGA splitter supports displays with up to 300 MHz of bandwidth and up to 2048x1536 resolution. Plus, to simplify placement of your VGA displays, the splitter features a built-in booster circuit that allows you to locate VGA monitors up to 200 ft away from your system.

The ST122LE VGA Splitter supports easy plug and play installation, and is backed by StarTech.com's 1-year warranty and FREE lifetime tech support.

Applications and Solutions

- Airports, bus terminals and train stations
- In-store product merchandising
- Information booths/kiosks
- Lecture halls and classrooms
- Quick and easy solution to split a video signal
- Trade-shows

Features

- 300 MHz bandwidth provides brilliant resolutions up to 2048 x 1536 60 Hz
- Compatible with VGA, SVGA, XGA, QXGA, UXGA and Multisync monitors
- Supports DDC, DDC2, DDC2B (For video out port 1)
- Will extend your video signal up to 65 meters (213 feet)

Technical Specifications

- Color: Black
- Connector Types: 1 - DB15 Male
- Connector Types: 2 - DB15 Female
- Enclosure Type: Plastic
- Input Current: Bandwidth: 300MHz
- Maximum Analog Resolutions: 2048x1536
- Number of Ports: 2
- Carton Quantity: 40
- Shipping (Package) Weight: 0.35 lb [0.16 kg]
- Power Adapter: DC 5V 500mA - USB Powered
- DDC Support: DDC, DDC2, DDC2B, on Video Out Port 1
- Max Distance: 65m / 210ft
- Storage Temp: -20°C - 85°C
- Operating Temp: 0°C - 70°C
- Operating Humidity: 0% - 95%