


4 Port High-Resolution 350 MHz VGA Video Splitter / Distribution Amplifier

StarTech ID: ST124PRO



The StarTech.com VideoView Pro is a High-End 4 port VGA Video Splitter that allows a PC to display to as many as 4 monitors simultaneously. It is perfect for presentations, classrooms, tradeshows, or in-store displays where the highest quality video on several monitors is needed. The VideoView Pro supports monitors with up to 350MHz of bandwidth allowing it to display images of 2048 x 1536 pixels or higher. A built-in booster circuit allows the video signal to be extended up to 200 ft.

Applications and Solutions

- Demos and presentations
- In-store product merchandising
- Information kiosks
- Public broadcast systems

Features

- Allows one computer to provide simultaneous displays for up to 4 different monitors
- Built-in video amplifier boosts the signal to allow a cable length of up to 210 ft or 65m
- Daisy chainable for almost unlimited expansion
- DDC compatible (all other monitors must be able to support the highest video resolution of the DDC-type monitor connected to Video Out 1)
- High video bandwidth (350 Mhz) provides crystal clear 2048 x 1536 resolution
- Includes AC 120V power adapter
- Uses standard monitor extension cables
- Works with VGA, SVGA and Multisync monitors

Technical Specifications

- Color: Black
- Connector Types: 4 - High Density 15 pin Female
- Connector Types: 1 - High Density 15 pin Male
- Product Height: 2.05 in [52 mm]
- Input Current: 0.2A
- Input Voltage: 9 DC
- Product Length: 8.82 in [224 mm]
- Maximum Analog Resolutions: 2048 x 1536
- Number of Ports: 4
- Power Adapter Included: Yes
- Power Adapter - Amperage: 0.6A
- Power Adapter - DC Voltage: 9V DC
- Carton Quantity: 12
- Shipping (Package) Weight: 2.03 lb [0.92 kg]
- Product Weight: 40.59 oz [1150 g]
- Product Width: 5.98 in [152 mm]
- Signal Type: XGA, VGA, SVGA, Multisync Monitor
- Cable Length: 65m (210 ft.) maximum
- Input Connector: High Density DB15 Male
- Output Connectors: (4) High Density DB15 Female
- VGA Bandwidth (-3db): 350 MHz
- VGA Resolution: 2046 x 1536 @ 80 Hz
- Operating Environment: 5~40 deg C, 0~80% RH non-condensing
- Dimensions: L6.8xW4.6xH1.6 in (224x152x52 mm)

- Weight: 1150g
- Certifications: FCC Part 15 Class A, CE Mark
- EDID Support: Yes