

## 42U 2 Post Open Frame Rack with Casters

StarTech ID: 2POSTRACK



This 42U 2 Post Open Frame Rack offers full steel construction instead of the aluminum used in competitive products, providing greater durability and stability that reduces the need for concrete mounting kits.

A cost-effective solution for mounting network equipment and telecom equipment, this two post rack features square mounting holes on the frame that allow you to easily mount ANSI/EIA RS-310-D compliant network equipment without additional hardware.

Easy to deploy, the two post open frame rack can be assembled in minutes and is backed by StarTech.com's Lifetime Warranty - ensuring a permanent server/telecom storage solution.

### Applications

- Server rooms or other locations where telecomm and networking equipment need to be housed

### Features

- Flat-packed design reduces handling costs
- Easy assembly at the point of installation for rapid deployment
- Full steel construction for superior durability and stability
- Mount standard networking equipment using standard cage nuts and screws

## Technical Specifications

Warranty	Lifetime
Casters	Included
U Height	42U
Frame Type	Open Frame
Wallmountable	No
Front Door Type	Open
Industry Standards	DIN41491 Part I
Industry Standards	DIN41491 Part VII
Industry Standards	EIA RS310-D
Industry Standards	GB/T3047.2-92
Industry Standards	IEC297-2
Fan(s)	No
Weight Capacity	331.5 lb [150 kg]
Color	Black
Internal Width	18.3 in [465 mm]
External Width	23.6 in [600 mm]
External Height	79.1 in [2008.7 mm]
External Depth	23.8 in [604 mm]
Product Weight	50.2 lb [22.7 kg]
Height with Casters	81.9 in [2080.7 mm]
Flat Pack	Yes
Shipping (Package) Weight	54.1 lb [24.5 kg]

## Certifications, Reports and Compatibility

