

8 Port 250 MHz VGA Video Splitter / Distribution Amplifier

StarTech ID: ST128



The StarTech.com VideoView is a 8 port VGA Video Splitter that allows a PC to display to as many as 8 monitors simultaneously. It is perfect for classrooms, tradeshow, or in-store displays where high quality video on several monitors is needed. The VideoView supports monitors with up to 200MHz of bandwidth allowing it to display images of up to 1600 x 1200 pixels. A built-in booster circuit allows the video signal to be extended up to 200 ft.

Applications and Solutions

- Demos and presentations
- In-store product merchandising
- Information kiosks
- Public broadcast systems
- Public information display services

Features

- Allows one computer to provide simultaneous displays on several different monitors
- Built-in video amplifier boosts the signal to allow a cable length of up to 210 ft or 65m
- Daisy chainable for almost unlimited expansion
- High/Low Level Brightness control
- Includes AC 120V power adapter
- Uses standard monitor extension cables
- Works with VGA, SVGA and Multisync monitors

Technical Specifications

- Color: Black
- Connector Types: 8 - High Density 15 pin Female
- Connector Types: 1 - High Density 15 pin Male
- Product Height: 2.05 in [52 mm]
- Input Voltage: 9
- Product Length: 8.82 in [224 mm]
- Maximum Analog Resolutions: 1600 x 1200
- Number of Ports: 8
- Power Adapter Included: Yes
- Power Adapter - Amperage: 0.6A
- Power Adapter - DC Voltage: 9V
- Carton Quantity: 5
- Shipping (Package) Weight: 4.07 lb [1.84 kg]
- Product Weight: 42.36 oz [1200 g]
- Product Width: 5.98 in [152 mm]
- Signal Type: XGA, VGA, SVGA, Multisync Monitor
- Cable Length: 65m (210 ft.) maximum
- Input Connector: High Density DB15 Male
- Output Connectors: (8) High Density DB15 Female
- VGA Bandwidth (-3db): 200 MHz
- VGA Resolution: 1600x1200 @ 60Hz
- Operating Environment: 5~40 deg C, 0~80% RH non-condensing
- Dimensions (LxWxH): 224x152x52 mm
- Weight: 1200g
- Certifications: FCC Part 15 Class A, CE Mark