

**6 ft Red Cat5e Crossover Snagless UTP Patch Cable**  
*StarTech ID: 45CROSS6RD*



StarTech.com's Cat5e UTP Snagless Crossover Patch Cables offer reliable Ethernet connections. This 6 ft cable meets all Category 5e specifications, and features a durable red jacket that simplifies departmental color coding while providing rugged flexibility for network connections.

To ensure long-lasting performance, our high quality Cat5e UTP Snagless Crossover Patch Cables feature a snagless design that protects the RJ45 clip from damage and makes the cables less prone to snagging during installation. The cables also feature PVC molded strain relief that prevents the RJ45 connector termination point from bending at sharp angles - reducing the risk of cable damage that could decrease network performance.

StarTech.com's 6 ft Red Cat5e UTP Snagless Crossover Patch Cable is constructed of only top quality materials to ensure optimum durability and is backed by our Lifetime Warranty.

### **Applications and Solutions**

- Connects workstation to workstation
- Patches from hub to hub

## Features

- Clip protector keeps the plug from snagging while routing the cable
- Coloured Hoods for departmental colour coding
- StarTech Category 5e patch cables are carefully constructed and tested, to keep the Near End Crosstalk (NEXT) well within acceptable limits
  - StarTech Category 5e Patch cables are constructed of top quality components
  - The Strain relief prevents the cable from being bent at sharp angles at the connector to minimize the stress at the plug termination point

## Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - RJ45 Male
- Connector B: 1 - RJ45 Male
- Color: Red
- Product Length: 6 ft [1.83 m]
- Maximum Cable Length: 328 ft [100 m]
- Network Cable Type: Crossover Snag-less
- Carton Quantity: 150
- Shipping (Package) Weight: 0.18 lb [0.08 kg]
- Length: 6 ft., 1.8m
- Connectors: RJ45 Male, RJ45 Male
- Cable: 24 AWG, 4 pair UTP, CAT-5e tested to 350 MHz, type CM (UL) certified, Category 5e

