

5m Multimode 50/125 Duplex Fiber Patch Cable LC - LC

StarTech ID: 50FIBLCLC5



The 50FIBLCLC5 5-meter (16ft) Multimode 50/125 Duplex Fiber Patch Cable is terminated at both ends with LC (male) connectors to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

Ensuring optimal data transfers and network stability, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Duplex 50/125 Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Features

- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Immune to electricity interference
- Attenuation loss meets or exceeds industry standards

Technical Specifications

| | |
|---------------------------|--|
| Warranty | Lifetime |
| Fiber Size | 50/125 |
| Connector A | 1 - Fiber Optic LC Male |
| Connector B | 1 - Fiber Optic LC Male |
| Fiber Classification | OM2 |
| Fiber Type | Multi Mode |
| Color | Orange |
| Cable Length | 16.4 ft [5 m] |
| Product Length | 16.4 ft [5 m] |
| Shipping (Package) Weight | 0.1 lb [0.1 kg] |
| Included in Package | 1 - 5m Multimode 50/125 Duplex Fiber Patch Cable LC – LC |

Certifications, Reports and Compatibility

