

## 5m Multimode 50/125 Duplex Fiber Patch Cable LC - SC

StarTech ID: 50FIBLCSC5



This 5m LC/SC Duplex 50/125 Multimode Fiber Patch Cable provides the necessary connection between fiber networking devices for high-speed, long distance networks.

Ensuring optimal data transfers and network stability, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Duplex 50/125 Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

### Applications

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

### Features

- Attenuation loss meets or exceeds industry standards
- Immune to electricity interference
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty

## Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Connector A	1 - Fiber Optic LC Male
Connector B	1 - Fiber Optic SC Male
Fiber Classification	OM2
Fiber Type	Multi Mode
Color	Orange
Cable Length	16.4 ft [5 m]
Product Length	16.4 ft [5 m]
Shipping (Package) Weight	0.1 lb [0.1 kg]
Included in Package	1 - 5m Multimode 50/125 Duplex Fiber Patch Cable LC - SC

## Certifications, Reports and Compatibility

