

## 10m Multimode 50/125 Duplex Fiber Patch Cable MTRJ - MTRJ

StarTech ID: 50FIBMTMT10



Your company's backbone is its Network. Without a stable, reliable network your company can't communicate. A lack of communication means a loss of revenue. What do you do now? Enter the StarTech.com duplex 50/125 Multimode Fiber Optic patch cable assembly. This product provides the necessary link between Fiber networking devices for high-speed, long-distance networks. Ideal for Gigabit networks, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability. The same lifetime warranty that applies to all StarTech.com cables protects our customers from any problems they might encounter with our cables.

### Applications and Solutions

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

## Features

- Attenuation loss meets or exceeds industry standards
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty
- Immune to electricity interference

## Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - MT-RJ Male
- Connector B: 1 - MT-RJ Male
- Color: Orange
- Fiber Size: 50/125
- Fiber Type: Multi Mode
- Product Length: 32.8 ft [10 m]
- Carton Quantity: 64
- Shipping (Package) Weight: 0.15 lb [0.07 kg]
- Cable Length: : 10m (32.8 ft)
- Cable Type: : Duplex Multimode
- Fiber Size: : 50/125 micron
- Connectors: :
- Connector A: MT-RJ (male)
- Connector B: MT-RJ (male)

