

3m Multimode 50/125 Duplex Fiber Patch Cable MTRJ - MTRJ

StarTech ID: 50FIBMTMT3



This Multimode 50/125 Duplex Fiber Optic Patch Cable is terminated with two SC Fiber Male connectors on one end, and one MT-RJ Male connector on the other, to provide the necessary link between Fiber networking devices for high-speed, long-distance networks. Ideal for Gigabit networks, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Multimode 50/125 Duplex Fiber Optic Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability. The same lifetime warranty that applies to all StarTech.com cables protects our customers from any problems they might encounter with our cables.

Applications

- Used by long distance networks with mission critical data
- Telecommunication / Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- Attenuation loss meets or exceeds industry standards
- Immune to electricity interference
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty

Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Connector A	1 - Fiber Optic MT-RJ Male
Connector B	1 - Fiber Optic MT-RJ Male
Fiber Classification	OM2
Fiber Type	Multi Mode
Color	Orange
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3 m]
Shipping (Package) Weight	0.1 lb [0 kg]