

42U 2 Post Open Frame Rack with Casters

StarTech ID: 2POSTRACK



This 42U 2 Post Open Frame Rack offers full steel construction instead of the aluminum used in competitive products, providing greater durability and stability that reduces the need for concrete mounting kits.

A cost-effective solution for mounting network equipment and telecom equipment, this two post rack features square mounting holes on the frame that allow you to easily mount ANSI/EIA RS-310-D compliant network equipment without additional hardware.

Easy to deploy, the two post open frame rack can be assembled in minutes and is backed by StarTech.com's Lifetime Warranty - ensuring a permanent server/telecom storage solution.

Applications and Solutions

- Server rooms or other locations where telecomm and networking equipment need to be housed

Features

- Easy assembly at the point of installation for rapid deployment
- Flat-packed design reduces handling costs
- Full steel construction for superior durability and stability
- Mount standard networking equipment using standard cage nuts and screws

Technical Specifications

- Warranty: Lifetime warranty
- Carton Quantity: 1
- Shipping (Package) Weight: 54.15 lb [24.5 kg]
- Product Weight: 50.17 lb [22.7 kg]
- Color: Black
- Weight Capacity: 331.5 lb [150 kg]
- Frame Type: : Steel
- Casters:: Included
- External Height : 79.08 in [2008.7 mm]
- External Width : 23.62 in [600 mm]
- External Depth : 23.62 in [600 mm]
- Internal Width: 19 in [482.6 mm]
- U Height: 42
- Height with Casters:: 81.92 in [2080.7 mm]
- Industry Standards: EIA RS310-D
- Industry Standards: IEC297-2
- Industry Standards: GB/T3047.2-92
- Industry Standards: DIN41491 Part I
- Industry Standards: DIN41491 Part VII

