

12U Adjustable 4 Post Server Equipment Open Frame Rack

StarTech ID: 4POSTRACK12



StarTech.com's DuraRak 12U, 4 Post Open Frame Rack/Cabinet provides a durable, open air housing for rackmount servers and networking equipment.

The equipment rack/cabinet features heavy gauge mounting rails to ensure a stable installation platform and adjustable posts for flexible installation.

The 12U open frame rack is compliant with EIA-RS-310C standards, offering a universal design that's compatible with equipment from popular manufacturers. Plus, the equipment rack is flat-packed, reducing shipping costs and simplifying handling and assembly.

For even more versatility, StarTech.com offers an optional [4pc Caster Kit](#) (4POSTCASTER) that can be installed on the bottom of the 12U server rack, making it easier to re-position the cabinet/rack as needed for future uses.

StarTech.com also offers the following Open Frame 4-Post Rack/Cabinets:

- [25U Open 4 Post Rack/Cabinet](#)
- [36U Open 4 Post Rack/Cabinet](#)
- [42U Open 4 Post Rack/Cabinet](#)

Applications and Solutions

- Audio/Video editing room, radio or television studio broadcast rackmount equipment
- Durable storage for rackmount servers, KVM switches, and networking equipment
- Great for satellite offices, and retail locations where a small amount of server equipment is setup
- Mounting equipment under a desk/workspace
- Perfect solution for Technology shops and repair centers with limited space and mountable equipment
- Suitable for rackmount equipment where security at the rack level is not required
- Useful for point of sale applications, specifically mounting equipment under the check-out counter

Features

- Adjustable mounting rails ensure broad equipment compatibility
- Heavy gauge mounting rails
- Pre-drilled base
- Unobstructed ventilation

Technical Specifications

- Warranty: Lifetime warranty
- Color: Black
- Carton Quantity: 1
- Shipping (Package) Weight: 69.84 lb [31.6 kg]
- Product Weight: 61.88 lb [28 kg]
- U Height: 12
- Weight Capacity: 552.5 lb [250 kg]
- Frame Type: : Steel
- Casters:: Optional
- External Height : 25.46 in [646.6 mm]
- External Width : 22.48 in [571 mm]
- External Depth : 39.37 in [1000 mm]
- Internal Height: 21.13 in [536.6 mm]
- Internal Width: 17.76 in [451 mm]
- Maximum Mounting Depth:: 35.25 in [895.35 mm]
- Minimum Mounting Depth:: 18.5 in [469.9 mm]
- Industry Standards: EIA RS310-C

