

## 3m Multimode 50/125 Duplex Fiber Patch Cable LC - LC

StarTech ID: 50FIBLCLC3



The 50FIBLCLC3 3-meter (10ft) Multimode 50/125 Duplex Fiber Patch Cable is terminated at both ends with LC (male) connectors to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

Ensuring optimal data transfers and network stability, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Duplex 50/125 Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

### Applications

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

### Features

- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Immune to electricity interference
- Attenuation loss meets or exceeds industry standards

## Technical Specifications

Warranty	Lifetime
Fiber Size	50/125
Connector A	1 - Fiber Optic LC Male
Connector B	1 - Fiber Optic LC Male
Fiber Classification	OM2
Fiber Type	Multi Mode
Color	Orange
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3 m]
Product Weight	0.1 lb [0 kg]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 3m Multimode 50/125 Duplex Fiber Patch Cable LC – LC

## Certifications, Reports and Compatibility

