

Aluminum ATA/133 Removable Drive Drawer

StarTech ID: DRW150ATA



StarTech.com's DRW150ATA is an ideal removable drive enclosure for switching between multiple operating systems, making high-speed, high-capacity backups or for other applications requiring frequent removal and insertion of mobile hard drives. This removable storage solution features a locking mechanism to prevent the drive from being accidentally removed while in use and a 25K Insertion Rating.

The DRW150ATA's compact, durable aluminum construction makes the drive enclosure easy to transport while helping to dissipate heat away from the drive.

Applications

- Removable drive drawers can be used in homes, at work, offices and in schools
- Mobile solution for high-capacity databases and large applications
- A fast and easy way to make backup copies of your files, applications and company's critical data

Features

- Secure and affordable solution to store and transfer data
- Ball-bearing fan maintains optimum cooling and increased air flow
- LED indicators continuously show the operating status of the drive drawer
- Supports hard drive ATA66/ATA100 & ATA133 with data transfer rates up to 133 MB/s
- Screw type stopper to avoid cover vibration while the HDD is working
- Supports hot swap and hot plug-in
- Compatibility with PC and MAC's
- Key lock mechanism prevents a hard drive from being accidentally removed while in operation
- All aluminum construction for maximum durability and heat dissipation

Technical Specifications

Warranty	Lifetime
Key Lock	Yes
Fans	1 - 40 mm
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Female
Connector Type(s)	1 - IDE (40 Pin; EIDE/PATA) Male
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Certifications	CE
Cooling Fan	Ball-Bearing Fan
CPU Compatibility	PC or Mac with a 5.25 Inch Drive Bay
Drive Drawer	
Dimensions	
Drive Drawer Enclosure	Aluminum
Enclosure Color	Beige
External Connectors	Header: 40 Pin Male & LP4: 4 Pin Female
Fan Dimensions	1.57 x 1.57 x 0.39 Inches (40 x 40 x 10 mm)
Fan Enclosure	Plastic
Hard Drive Compatibility	All 3.5-Inch IDE Hard Drives
Inches	9.00 x 5.75 x 1.61
Internal Connectors	Header: 40 Pin Female & LP4: 4 Pin Female
LED Indicators	Drive Activity & Drive Power
Millimeters	220 x 148 x 41
Note	Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
Weight (w/o drive)	1.90 Lbs (0.86 Kgs)
Color	Beige
Enclosure Type	Aluminum
Product Length	8.7 in [220 mm]
Product Width	5.8 in [148 mm]
Product Height	1.6 in [41 mm]
Product Weight	30.4 oz [860 g]
LED Indicators	1 - Activity
LED Indicators	1 - Power

Shipping (Package) Weight 2.1 lb [0.9 kg]

Certifications, Reports and Compatibility

