

3m Multimode 50/125 Duplex Fiber Patch Cable MTRJ - MTRJ

StarTech ID: 50FIBMTMT3



This Multimode 50/125 Duplex Fiber Optic Patch Cable is terminated with two SC Fiber Male connectors on one end, and one MT-RJ Male connector on the other, to provide the necessary link between Fiber networking devices for high-speed, long-distance networks. Ideal for Gigabit networks, 50/125-micron cables offer nearly three times the bandwidth of 62.5/125-micron cables, so your data will be transferred at higher rates over longer distances.

Each Multimode 50/125 Duplex Fiber Optic Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability. The same lifetime warranty that applies to all StarTech.com cables protects our customers from any problems they might encounter with our cables.

Applications and Solutions

- Broadband systems
- Ideal solution for data applications requiring high speed data transmission
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

Features

- Attenuation loss meets or exceeds industry standards
- Connectors offer greater durability in resisting pulls, strains, and impacts during cable installation and maintenance
- Fiber Optic Cables are backed by StarTech.com's lifetime warranty
- Immune to electricity interference

Technical Specifications

- Warranty: Lifetime warranty
- Connector A: 1 - MT-RJ Male
- Connector B: 1 - MT-RJ Male
- Color: Orange
- Fiber Size: 50/125
- Fiber Type: Multi Mode
- Product Length: 9.84 ft [3 m]
- Carton Quantity: 60
- Shipping (Package) Weight: 0.07 lb [0.03 kg]
- Cable Length: : 3m (9.6 ft)
- Cable Type: : Duplex Multimode
- Fiber Size: : 50/125 micron
- Connectors: :
- Connector A: MT-RJ (male)
- Connector B: MT-RJ (male)