

## 10U 19in Wall Mounted Server Rack Cabinet

StarTech ID: CAB1019WALL



This 10U Wall Mounted Server Rack Cabinet can be mounted to most wall materials, allowing you to securely position your rackmount equipment exactly as needed.

The server rack offers 10U of storage space and is designed to accommodate 19in (wide) equipment. To ensure a cool operating environment for your networking equipment, the server rack includes a 5in roof-mounted fan (85 CFM) and vented side panels - not only helping to keep temperatures down, but keep dust out of the rack.

To secure network equipment from tampering, the cabinet features a lockable, smoked acrylic front door, that can be removed entirely or installed to open to the left or right as needed.

### Applications

- Data centers
- Industrial control centers
- Telecommunication closets
- Audio/Visual control centers

### Features

- Fully adjustable mounting rails inside cabinet
- Front door is removable and can be switched to open left or right
- One roof-mounted fan exhaust up to 85 CFM of air
- Comes fully assembled
- Includes (1) 5" (12cm) Ball bearing AC fan moving up to 85 CFM of air, lockable & removable smoked acrylic front door with 2 keys
- Stylish enclosure is designed for durability and easy accessibility

## Technical Specifications

Warranty	Lifetime
U Height	10U
Frame Type	Enclosed Cabinet
Wallmountable	Yes
Front Door Type	Steel w/ Window
Key Lock	Yes
Industry Standards	EIA RS310-C
Fan(s)	Yes
Fans	1 - 5 Inch
Weight Capacity	132.6 lb [60 kg]
Air Flow Rate	85 CFM
Noise Level	36 dBA
Color	Beige
Internal Width	18.3 in [465 mm]
Internal Height	17.6 in [448 mm]
Internal Depth	22.7 in [576.6 mm]
External Width	22 in [560 mm]
External Height	20 in [508 mm]
External Depth	23.6 in [600 mm]
Product Weight	48.6 lb [22 kg]
Maximum Mounting Depth	17.7 in [450.9 mm]
Input Voltage	115 AC
Input Current	180 mA
Flat Pack	No
Shipping (Package) Weight	51.2 lb [23.2 kg]

## Certifications, Reports and Compatibility

