

## 120x25mm Dual Ball Bearing Computer Case Fan w/ LP4 Connector

StarTech ID: FANBOX12



This versatile 12cm PC case fan is designed to fit a broad range of computer case designs, to circulate cool air into the case, or exhaust warm air out - preventing problems due to overheating components.

A quiet cooling solution, the 12cm dual ball-bearing case fan features a high efficiency blade design that's capable of moving 72.94 CFM throughout the computer case, helping to optimize system performance.

This broadly compatible PC cooling solution can be powered through a simple LP4 connection to the computer power supply, and is backed by StarTech.com's 2-year warranty.

### Applications and Solutions

- Replace a noisy or failed computer case fan
- Install into a computer to increase air flow and cooling

## Features

- Inline LP4 power connectors
- Dual ball bearing design

## Technical Specifications

- Warranty: 2 Years
- Air Flow Rate: 72.94 CFM
- Cable Length: 12 in [304.8 mm]
- Product Height: 4.72 in [120 mm]
- Input Current: LP4 Male connector - 10 inches
- Product Length: 4.72 in [120 mm]
- Noise Level: 30 dBA
- Number of Conductors: 2
- Operating Temperature: -10 to 80
- Carton Quantity: 60
- RPM: 2000
- Shipping (Package) Weight: 0.44 lb [0.2 kg]
- Product Weight: 6.39 oz [181 g]
- Product Width: 0.98 in [25 mm]

