

120x25mm Dual Ball Bearing Computer Case Fan w/ LP4 Connector

StarTech ID: FANBOX12



This versatile 12cm PC case fan is designed to fit a broad range of computer case designs, to circulate cool air into the case, or exhaust warm air out - preventing problems due to overheating components.

A quiet cooling solution, the 12cm dual ball-bearing case fan features a high efficiency blade design that's capable of moving 72.94 CFM throughout the computer case, helping to optimize system performance.

This broadly compatible PC cooling solution can be powered through a simple LP4 connection to the computer power supply, and is backed by StarTech.com's 2-year warranty.

Applications

- Replace a noisy or failed computer case fan
- Install into a computer to increase air flow and cooling

Features

- Dual ball bearing design
- Inline LP4 power connectors

Technical Specifications

Warranty	2 Years
Number of Conductors	2
Fan Bearing Type	Ball Bearing
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Female
Connector Type(s)	1 - LP4 (4 pin; Molex Large Drive Power) Male
Fan RPM	2000
Air Flow Rate	72.94 CFM
Noise Level	30 dBA
Color	Black
Enclosure Type	Plastic
Cable Length	12 in [304.8 mm]
Product Length	4.7 in [120 mm]
Product Width	1 in [25 mm]
Product Height	4.7 in [120 mm]
Product Weight	6.4 oz [181 g]
Input Voltage	12 DC
Input Current	LP4 Male connector - 10 inches
Operating Temperature	-10 to 80
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - 12cm Case Fan
Included in Package	4 - Mounting Screws

Certifications, Reports and Compatibility

