

Value 5.25in Durable SATA Hard Drive Mobile Rack Drawer

StarTech ID: DRW110SAT



Capable of delivering transfer rates of up to 3 Gb/sec, StarTech.com's DRW110SAT removable SATA hard drive enclosure allows you to harness the power of SATA/150 and SATA/300(SATA II) hard drives. This removable enclosure is a cost-effective way to quickly insert or remove SATA hard drives from any PC with an available 5.25-inch drive bay without opening the computer case. Ideal solution for high-speed back-ups, moving large files from one computer to another, and for running multiple operating systems on the same PC.

While providing security and minimizing downtime, the DRW110SAT features reliable shock absorbers that help limit physical damage to the enclosed hard drive during transport.

Applications and Solutions

- Easily transport massive databases, space consuming multimedia files, archived data, as well as other large files, from one location to another
- Great for institutions and individuals replacing IDE/Parallel ATA hard drives with SATA/300(SATA II) or SATA/150 hard drives
- Removable drive enclosure can be used in homes, at work, offices and in schools
- Use multiple operating systems on one computer and share a PC with your kids without worrying about your business data and valuable information stored in the hard drive

Features

- Compatibility with both PC and Mac systems
- Designed with a power controlled key lock mechanism to prevent the hard drive from being accidentally removed while in operation
- Hard drive cooling is provided by a rear mounted ball-bearing fan
- LED indicator continuously showing the operating status of the drive drawer
- Shock absorber system and rubber cushions protect your hard drive from shock, vibration and rough handling
- Smaller SATA connectors and thinner SATA cables maximize cooling and system air flow
- Supports SATA/300(SATA II) SATA/150 hard drives with data transfer rates of up to 3 Gb/sec. (300 MB/s)
- The frame and caddy is constructed with high quality plastic for extra durability

Technical Specifications

- Warranty: 1 Year warranty
- Color: Beige
- Product Height: 1.61 in [41 mm]
- LED Indicators: 1 - Power
- Carton Quantity: 20
- Shipping (Package) Weight: 1.26 lb [0.57 kg]
- HD Compatibility: All 3.5 Inch SATA/300(SATA II) or SATA/150 (SATA I) Hard Drives
- CPU Compatibility: PC or Mac with a 5.25 Inch Drive Bay
- Weight (w/o drive): 1.15 lbs (0.53 kg)
- Connectors:
 - Internal: Header – 7 Pin Female, LP4 – 4 Pin Female
 - External: Header – 7 Pin Male, LP4 – 4 Pin Male
- Dimensions:
 - Inches: 8.6 x 5.75 x 1.61
 - Millimeters: 220 x 148 x 41
- LED Indicator(s):
 - Drive Power: Green
- Cooling Fan: Ball-Bearing Fan
- Drive Drawer Enclosure: Plastic
- Enclosure Color: Beige
- Fan Dimensions: Inches: 1.57 x 1.57 x 0.39 Millimeters: 40 x 40 x 10

- Certifications: CE
- Note: Unit is model specific and is not meant for use with different models of drive drawer unless otherwise stated
- Drive Type: Supports up to 750Gb hard drive capacity

